



<b>H (mm - U)</b>	<b>T (mm)</b>	<b>B (mm)</b>	<b>h1 (mm)</b>	<b>h2 (mm)</b>	<b>h3 (mm)</b>	<b>t1 (mm)</b>	<b>t2 (mm)</b>	<b>b1 (mm)</b>
1530 - 29U	600	1300	1305	100	124	503	615	1136