



# CGHD

Ref.	Pic.	Qty.
A		5
B		5

Item	View 1	View 3	View 3	View 3	View 4	View 4
CGHD12	∅ 12mm	15mm	7mm	6.0 Nm	14mm	2.5 Nm
CGHD16	∅ 16mm	19mm	10mm	9.0 Nm	18mm	4.0 Nm
CGHD20	∅ 20mm	24mm	13mm	12.0 Nm	22mm	5.0 Nm
CGHD25	∅ 25mm	30mm	17mm	14.0 Nm	28mm	6.0 Nm

