






客户信息/ECN No.	ECN 编号	图样标记	数量	版本	签名	日期
客户号/REV.	图号/PN	ECN No.	Drawing mark	Places	REV.	Date
--	--	--	--	--	E1	20200420



**SPECIFICATION:**

1. STANDARD:

UNIT TYPE:	MONITORED SWITCHED
ORIENTATION:	VERTICAL, 0U FULL
OUTLET QTY & TYPE:	(30)C13, (6)C19
INPUT VOLTAGE:	100-120/200-240VAC
INPUT CURRENT:	30A (24A DERATED)
BREAKER QTY & TYPE:	(3) 20AMP, DOUBLE-POLE
INPUT PHASE:	THREE-PHASE, WYE
RATED POWER:	8.6 KVA
INPUT PLUG:	NEMA L21-30P
INPUT POWER CORD:	3m[10'], TOP FEED
REGULATORY STANDARD:	RoHS COMPLIANT



	<b>PLUG</b> NEMA L21-30P, 4P 5W 30A, 120/208V MAX RATED INPUT 24A DERATED
	<b>RECEPTACLES</b> IEC 60320/C19 16A, 250V MAX RATED OUTPUT
	<b>RECEPTACLES</b> IEC 60320/C13 10A, 250V MAX RATED OUTPUT

<b>CISGLOBAL</b>				项目	EN2.0	阶段标记	
				Project	EN2.0	S	
泛亚电子工业无锡有限公司				图号	TA-EN2804A		
设计/Design	Jingbo Luo	日期/Date	2020.05.20	名称	PDU	重量/Weight	N/A
审核/Check	Aric Wang	日期/Date	2020.05.20	Title		比例/Scale	1:3
工艺检查/Review	Talon LV	日期/Date	2020.05.20	材料	Assembly	幅面/Size	A2
批准/Approve	Hanson Xu	日期/Date	2020.05.20	Material		共1页	第1页