

Global IEC Enclosure Portfolio



HOFFMAN

CONNECT AND PROTECT

Redefine simplicity when ordering and assembling

nVent HOFFMAN's comprehensive Global IEC rated standard product range includes mild steel and stainless steel floor stand, wall mount and terminal box enclosure solutions. Accelerate the specification and installation process through interchangeable accessories and tool-free assembly, while streamlining ordering with a single global part number.

01 FAST ASSEMBLY

02 OPTIMUM PROTECTION

03 APPEALING DESIGN



BENEFITS



Patented tool-free, Click-In Technology reducing assembly time by 14 minutes when buying floor stand enclosures.



Single universal part number to service customers across the globe.



Vast library of digital drawing formats for every product to fit almost any design platform.



Multiple interchangeable accessories for product versatility across wall mount and floor stand offerings.

CREATING A MORE SUSTAINABLE AND ELECTRIFIED WORLD

At nVent, we believe safer systems ensure a more secure world. We connect and protect with inventive electrical solutions. nVent HOFFMAN creates enclosures that boost system resiliency by protecting critical components to extend system lifespan, overall reducing cost and waste.



Resiliency and Protection



Lifespan and Serviceability



Safety

TAKE YOUR PICK!

FLOOR STANDING



MCS, MCD, MCF, MCSS, MCDS		
	Single Door:	Double Door
Material:	Mild and Stainless Steel (AISI 304L and 316L)	
Height:	1400-2200	1400-2200
Width:	400-1000	1000-1800
Depth:	400-800	500-800
Water/Dust Protection:	IP55, Type 3R, Type 12	IP55, Type 12
	HP Models: IP66, Type 4, 4X	
Impact Resistance:	IK 10	
Frame:	Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660	
Removable Panels:	All panels are removable, allowing for ease of machining and customization	
Mount Plate:	Double folded and slides into position; rear-most position mounting standard	

WALL MOUNT



MAS, ASR, MAD, ADR		
	Single Door:	Double Door
Material:	Mild and Stainless Steel (AISI 304L and 316L)	
Height:	200-1400	600-1400
Width:	200-800	800-1200
Depth:	150-400	210-400
Water/Dust Protection:	IP66, Type 4X, 4, 12	IP55, Type 12
Impact Resistance:	IK 10	
Gasket:	Injected one piece polyurethane	
Locking:	One lock, two locks & 3-point latch	3-point latch
Gland Plate:	One opening	Two openings

TERMINAL BOX



STB, SSTB	
Material:	Mild and Stainless Steel 304
Height:	150-400
Width:	150-800
Depth:	80-120
Water/Dust Protection:	IP66, Type 4X, 4, 12
Impact Resistance:	IK 08
Gasket:	Injected one piece polyurethane, silicone in stainless steel 316 versions
Locking:	Quarter turn screws fitted to laser cut corner brackets



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER