

ITEM (Item no.)	MAS0202015R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 200x200x155
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	200
W (Width / mm)	200
D (Depth / mm)	155
MPH (Mounting Plate Height / mm)	170
MPW (Mounting Plate Width / mm)	150
DMAX (Max. enclosure useful depth / mm)	137
MASS (Weight / kg)	2.95
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	110
DGP (Depth Gland Plate)	56
EAN (EAN Code)	8713574123885
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

