

ITEM (Item no.)	MAS0403015R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 400x300x155
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	400
W (Width / mm)	300
D (Depth / mm)	155
MPH (Mounting Plate Height / mm)	370
MPW (Mounting Plate Width / mm)	250
DMAX (Max. enclosure useful depth / mm)	137
MASS (Weight / kg)	6.75
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	210
DGP (Depth Gland Plate)	56
EAN (EAN Code)	8713574125551
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

