

ITEM (Item no.)	MAS0503021R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 500x300x210
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	500
W (Width / mm)	300
D (Depth / mm)	210
MPH (Mounting Plate Height / mm)	470
MPW (Mounting Plate Width / mm)	250
DMAX (Max. enclosure useful depth / mm)	192
MASS (Weight / kg)	8.95
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	210
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128835
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

