

ITEM (Item no.)	MAS0504015R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 500x400x155
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	500
W (Width / mm)	400
D (Depth / mm)	155
MPH (Mounting Plate Height / mm)	470
MPW (Mounting Plate Width / mm)	350
DMAX (Max. enclosure useful depth / mm)	137
MASS (Weight / kg)	10.4
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	310
DGP (Depth Gland Plate)	56
EAN (EAN Code)	8713574128811
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

