

| | |
|---|---------------------------|
| ITEM (Item no.) | MAS0504021R5 |
| DETAIL () | low |
| INFO (Info PDF) | Info PDF |
| DES (Description) | Wall mounted, 500x400x210 |
| MPL (Mounting plate) | With mounting plate |
| MAT (Material) | Mild steel |
| LOCKS (No. of locks) | 1 |
| H (Height / mm) | 500 |
| W (Width / mm) | 400 |
| D (Depth / mm) | 210 |
| MPH (Mounting Plate Height / mm) | 470 |
| MPW (Mounting Plate Width / mm) | 350 |
| DMAX (Max. enclosure useful depth / mm) | 192 |
| MASS (Weight / kg) | 11.35 |
| NOGP (No. of Gland Plate Openings) | 1 |
| WGP (Width Gland Plate) | 310 |
| DGP (Depth Gland Plate) | 96 |
| EAN (EAN Code) | 8713574128910 |
| TARIFFN (Tariff numbers) | 94032080 |
| MI (Mounting Instructions) | URL |

