

ITEM (Item no.)	MAS0505021R5
DETAIL ()	low
INFO (Info PDF)	<a href="#">Info PDF</a>
DES (Description)	Wall mounted, 500x500x210
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	500
W (Width / mm)	500
D (Depth / mm)	210
MPH (Mounting Plate Height / mm)	470
MPW (Mounting Plate Width / mm)	450
DMAX (Max. enclosure useful depth / mm)	192
MASS (Weight / kg)	13.45
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	410
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574129276
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	<a href="#">URL</a>

