

ITEM (Item no.)	MAS0505030R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 500x500x300
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	500
W (Width / mm)	500
D (Depth / mm)	300
MPH (Mounting Plate Height / mm)	470
MPW (Mounting Plate Width / mm)	450
DMAX (Max. enclosure useful depth / mm)	282
MASS (Weight / kg)	15.6
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	410
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574129252
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

