

ITEM (Item no.)	MAS0604021R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 600x400x210
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	600
W (Width / mm)	400
D (Depth / mm)	210
MPH (Mounting Plate Height / mm)	570
MPW (Mounting Plate Width / mm)	350
DMAX (Max. enclosure useful depth / mm)	192
MASS (Weight / kg)	13.65
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	310
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574129214
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

