

ITEM (Item no.)	MAS0605021R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 600x500x210
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	600
W (Width / mm)	500
D (Depth / mm)	210
MPH (Mounting Plate Height / mm)	570
MPW (Mounting Plate Width / mm)	450
DMAX (Max. enclosure useful depth / mm)	192
MASS (Weight / kg)	16.25
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	410
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574129139
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

