

ITEM (Item no.)	MAS0606021R5
DETAIL ( )	low
INFO (Info PDF)	<a href="#">Info PDF</a>
DES (Description)	Wall mounted, 600x600x210
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	600
W (Width / mm)	600
D (Depth / mm)	210
MPH (Mounting Plate Height / mm)	570
MPW (Mounting Plate Width / mm)	550
DMAX (Max. enclosure useful depth / mm)	192
MASS (Weight / kg)	21.9
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	510
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574129078
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	<a href="#">URL</a>

