

ITEM (Item no.)	MAS0608030R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 600x800x300
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	600
W (Width / mm)	800
D (Depth / mm)	300
MPH (Mounting Plate Height / mm)	570
MPW (Mounting Plate Width / mm)	750
DMAX (Max. enclosure useful depth / mm)	282
MASS (Weight / kg)	31.45
NOGP (No. of Gland Plate Openings)	2
WGP (Width Gland Plate)	310
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128477
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

