

ITEM (Item no.)	MAS0705021R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 700x500x210
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	700
W (Width / mm)	500
D (Depth / mm)	210
MPH (Mounting Plate Height / mm)	670
MPW (Mounting Plate Width / mm)	450
DMAX (Max. enclosure useful depth / mm)	192
MASS (Weight / kg)	21.5
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	410
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128453
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

