

|   |                           |
|---|---------------------------|
| ITEM (Item no.)                         | MAS0804030R5              |
| DETAIL ()                               | low                       |
| INFO (Info PDF)                         | <a href="#">Info PDF</a>  |
| DES (Description)                       | Wall mounted, 800x400x300 |
| MPL (Mounting plate)                    | With mounting plate       |
| MAT (Material)                          | Mild steel                |
| LOCKS (No. of locks)                    | 2                         |
| H (Height / mm)                         | 800                       |
| W (Width / mm)                          | 400                       |
| D (Depth / mm)                          | 300                       |
| MPH (Mounting Plate Height / mm)        | 770                       |
| MPW (Mounting Plate Width / mm)         | 350                       |
| DMAX (Max. enclosure useful depth / mm) | 282                       |
| MASS (Weight / kg)                      | 22.05                     |
| NOGP (No. of Gland Plate Openings)      | 1                         |
| WGP (Width Gland Plate)                 | 310                       |
| DGP (Depth Gland Plate)                 | 96                        |
| EAN (EAN Code)                          | 8713574128415             |
| TARIFFN (Tariff numbers)                | 94032080                  |
| MI (Mounting Instructions)              | <a href="#">URL</a>       |

