

ITEM (Item no.)	MAS0806026R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 800x600x260
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	800
W (Width / mm)	600
D (Depth / mm)	260
MPH (Mounting Plate Height / mm)	770
MPW (Mounting Plate Width / mm)	550
DMAX (Max. enclosure useful depth / mm)	242
MASS (Weight / kg)	28.6
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	510
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128514
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

