

ITEM (Item no.)	MAS0806040R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 800x600x400
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	2
H (Height / mm)	800
W (Width / mm)	600
D (Depth / mm)	400
MPH (Mounting Plate Height / mm)	770
MPW (Mounting Plate Width / mm)	550
DMAX (Max. enclosure useful depth / mm)	382
MASS (Weight / kg)	35.2
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	510
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128330
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

