

ITEM (Item no.)	MAS1006030R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 1000x600x300
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	1000
W (Width / mm)	600
D (Depth / mm)	300
MPH (Mounting Plate Height / mm)	970
MPW (Mounting Plate Width / mm)	550
DMAX (Max. enclosure useful depth / mm)	282
MASS (Weight / kg)	39.15
NOGP (No. of Gland Plate Openings)	1
WGP (Width Gland Plate)	510
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128774
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

