

|   |                            |
|---|----------------------------|
| ITEM (Item no.)                         | MAS1008030R5               |
| DETAIL ()                               | low                        |
| INFO (Info PDF)                         | <a href="#">Info PDF</a>   |
| DES (Description)                       | Wall mounted, 1000x800x300 |
| MPL (Mounting plate)                    | With mounting plate        |
| MAT (Material)                          | Mild steel                 |
| LOCKS (No. of locks)                    | 1                          |
| H (Height / mm)                         | 1000                       |
| W (Width / mm)                          | 800                        |
| D (Depth / mm)                          | 300                        |
| MPH (Mounting Plate Height / mm)        | 970                        |
| MPW (Mounting Plate Width / mm)         | 750                        |
| DMAX (Max. enclosure useful depth / mm) | 282                        |
| MASS (Weight / kg)                      | 49.2                       |
| NOGP (No. of Gland Plate Openings)      | 2                          |
| WGP (Width Gland Plate)                 | 310                        |
| DGP (Depth Gland Plate)                 | 96                         |
| EAN (EAN Code)                          | 8713574128736              |
| TARIFFN (Tariff numbers)                | 94032080                   |
| MI (Mounting Instructions)              | <a href="#">URL</a>        |

