

ITEM (Item no.)	MAS1008040R5
DETAIL ()	low
INFO (Info PDF)	Info PDF
DES (Description)	Wall mounted, 1000x800x400
MPL (Mounting plate)	With mounting plate
MAT (Material)	Mild steel
LOCKS (No. of locks)	1
H (Height / mm)	1000
W (Width / mm)	800
D (Depth / mm)	400
MPH (Mounting Plate Height / mm)	970
MPW (Mounting Plate Width / mm)	750
DMAX (Max. enclosure useful depth / mm)	382
MASS (Weight / kg)	54.15
NOGP (No. of Gland Plate Openings)	2
WGP (Width Gland Plate)	310
DGP (Depth Gland Plate)	96
EAN (EAN Code)	8713574128712
TARIFFN (Tariff numbers)	94032080
MI (Mounting Instructions)	URL

