

## MCS18044R5

Floor standing, 1800x400x400, Mild steel, Cable enclosures: without MP, bottom plates and door frame

ITEM (Item no.)	MCS18044R5
DETAIL ()	low
INFO (Info PDF)	<a href="#">Info PDF</a>
DES (Description)	Floor standing, 1800x400x400
MPL (Mounting plate)	Cable enclosures: without MP, bottom plates and door frame
MAT (Material)	Mild steel
H (Height / mm)	1800
W (Width / mm)	400
D (Depth / mm)	400
MPH (Mounting Plate Height / mm)	0
MPW (Mounting Plate Width / mm)	0
DMAX (Max. enclosure useful depth / mm)	0
MASS (Weight / kg)	51
EAN (EAN Code)	8713574129863
TARIFFN (Tariff numbers)	85381000
MI (Mounting Instructions)	<a href="#">URL</a>

