

# MC/AC Trapeze Support

## CONNECT AND PROTECT



The nVent CADDY MCS Trapeze (MCST) is a fast and cost-effective method for installing a wide range of MC/AC cable in overhead and trapeze installations. The MCST series eliminates the need for traditional fasteners, reducing installation time and material cost. The break-apart design feature makes it simple to field modify, providing an ideal solution for contractors looking to maximize installation efficiency.

### FEATURES

- Shot fire flange for direct attachment to ceiling/deck
- Easy to use break-apart feature for easy field modification
- Properly spaces MC/AC cable to help eliminate bundling and NEC® and CEC derating issues
- Up to 50% installation time savings over traditional methods

Finish: Pregalvanized  
Material: Steel



Catalog Number	MC/AC Cable Size	Super Neutral Cable Size	Outer Diameter OD	Cable Capacity	Length 1 (L1)	Length 2 (L2)	Height (H)	Hole Size 1 (HS1)	Hole Size 2 (HS2)
MCS101TX4	10-3 to 8-3	12-3 to 10-2	0.56 – 0.69 in	28	3 in	12 in	2.5 in	0.2 in	0.25 in
MCS101TX8	10-3 to 8-3	12-3 to 10-2	0.56 – 0.69 in	56	3 in	24 in	2.5 in	0.2 in	0.25 in
MCS100TX4	14-3 to 10-2	10-2	0.43 – 0.56 in	32	3 in	12 in	2.5 in	0.2 in	0.25 in
MCS100TX8	14-3 to 10-2	10-2	0.43 – 0.56 in	64	3 in	24 in	2.5 in	0.2 in	0.25 in

Accommodates 1/4" threaded rod trapeze drops.

