



CONNECT AND PROTECT

Trusted Data Center and Networking Solutions

For a Connected World

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER



Connected World

EVERY THING IS BECOMING CONNECTED
AND GETTING FASTER!

FROM THE EDGE TO THE CLOUD

Trust in nVent's optimized solutions for connecting and protecting mission critical data center and networking infrastructure.

The speed of changing technology creates significant new challenges for connecting and protecting data center and network infrastructure. Achievements of increased processing capacity, higher data latency and reduced operational costs are met with both expected and unexpected consequences. Multi-vendor systems create complexity. Busy connection pathways are stressed to their limits and new security threats emerge daily.

Ever-expanding IT and communication requirements demand remote equipment solutions in places where they never existed.

The highest amount of data and network availability is crucial in today's connected world. Our broad portfolio provides design flexibility and protection.



Ensure uptime of your infrastructure



Reduce planning and installation time




Minimize the operational costs



Maximize resources with service and support



CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER





Global Presence and Regional Support

ESTABLISHED AS ONE OF THE BEST

SAFETY

nVent manufacturing processes are conducted in accordance with ISO 9001 ensuring maximum operating efficiency for our manufacturing & assembly facilities.



SUPPORT

nVent experts to support you on-site all around the globe.

QUALITY

nVent solutions are designed according to regional and national safety standards.



**CUSTOMERS
ALWAYS
COME
FIRST**



INNOVATION

nVent connects and protects mission critical infrastructure and personnel by delivering tailored solutions based on our customer's challenges.

OUR MODULAR AND BROAD PORTFOLIO COMBINED WITH DESIGN AND PROJECT SUPPORT ENABLES YOU TO SPECIFY AND DEPLOY YOUR PROJECT ON TIME TO ENSURE DATA AND NETWORK INFRASTRUCTURE AVAILABILITY AND PROTECTION.



CADDY

nVent CADDY includes fixing, fastening, and support products for high performance cabling systems designed to save installation time.

RAYCHEM

nVent RAYCHEM TraceTek leak detection solutions pinpoint the source of water and fuel leaks, providing you with critical information to take swift action and avoid damage.

ERICO

nVent ERICO offers a full range of facility electrical protection products to protect data centers, network and other facilities.

HOFFMAN

nVent HOFFMAN offers a broad range of targeted networking enclosures and racks for protecting sensitive electronic equipment.

SCHROFF

nVent SCHROFF brand offers modular and scalable server cabinets, aisle containment systems and active cooling solutions to perfectly fit customers' data center requirements.



80+

Manufacturing, service, sales and distribution centres

30M+

nVent enclosures in use globally

400+

Patents

8800

Global Workforce

100+

years of innovation

Data Centers

PROTECTION FOR SMALL TO HYPERSCALE DATA CENTERS



SMART SERVER CABINETS

- Welded steel frame with static load 1,600 kg / 3,525 lbs.
- Modular customizable platforms
- 42RU, 47RU & 52RU standard heights, custom available
- 1000/1200 mm standard depths, custom available
- Colocation, seismic and NEMA rated cabinets available

SMART CABLE MANAGEMENT

- Flexible accessories for different cabling zones



SMART MONITORING

- Data center environmental monitoring platform
- Compact design fits anywhere in a data center rack
- Web browser GUI for setup and maintenance
- Three management ports to connect external sensors and Modbus devices
- Up to 16 sensors/Modbus devices per management port with a cable length of 40m
- LCD touch display
- Supports industry standard network protocols (HTTPS, SNMP, SMTP, BACnet, Modbus/TCP)



SMART LEAK DETECTION

- Leak detection sensors: water, fuel, caustic chemicals, and hydrocarbons
- Robust and reliable conductive sensing cables
- Interchangeable components allows modular configurations
- Advanced control and alarm panels



SMART RACK POWER

BASIC PDUs

- Provide convenient, reliable power to equipment
- Rack- and panel-mount models available

I-PDUs

- Metered and switched solutions in single and three phase versions
- Hot-pluggable meter and field replaceable PSU
- Metering accuracy within +/-1%





SMART AISLE CONTAINMENT

- Modular components to optimize data center air flow
- Designed to support different fire suppression systems
- 3 different door options: swing door, manual and automatic sliding doors
- Design allows easy integration of third party cabinets



SMART PRECISION AND HIGH DENSITY LIQUID COOLING

RACKCHILLER IN ROW

- Modular and scalable precision cooling solution
- Available in 2 different performance classes - Cooling performance of 55 kW (300 mm) and 75 kW (600 mm) in optimal operating conditions
- Built-in redundancy through EC fan technology

CLOSED LOOP MICRO DATA CENTER

- Integrated rack-based cooling solution
- Modular and scalable to rack level cooling requirements
- EMC-shielded, harsh environment as well as outdoor solutions available
- Reduced noise levels

RACKCHILLER REAR DOOR

- No noise, minimal power consumption, low maintenance
- Active solution - integrated fans supplement air flow and minimize pressure drop to ensure even distribution across the heat exchanger
- Frame separation solution allows separation of coil and condensate management from the rack-mount equipment Available in 6 standard dimensions

DIRECT-TO-CHIP COOLING

- Enables maximum heat dissipation in high-density racks
- Facilitate peak performance for higher powered processors
- May reduce dependence on fans and expensive air handling systems
- Reduce OPEX-utilizes warm water cooling and eliminates chilled water requirements




Optimized for up to 25 kW per Rack



Optimized for up to 25 kW per Rack



Optimized for up to 55 kW per Rack



Optimized for extreme high densities 40 kW - 500 kW+

IT/Networking

PROTECTION FOR NETWORKS IN BUILDINGS, CAMPUS AND INDUSTRIAL FLOOR SPACE



SMART NETWORKING RACKS AND CABINETS

WALL-MOUNT CABINETS

- Double-hinged or single-door cabinets
- Front and rear access to 19-in. rack-mounted equipment
- Protection against water, dirt, corrosive agents and other contaminants
- Broad range of sizes, materials and configurations
- Easy, one person installation
- Some models available with optional AC unit
- Models in NEMA Type 1, 3R, 4, 4X, 12

2- AND 4-POST OPEN FRAME RACKS

- Strong aluminum construction with RU markings on front and rear
- 4-post has adjustable depth for maximum versatility
- 2- and 4-post racks can be ganged
- 2500-lb. load capacity (4-post)
- Seismic versions



FREE STANDING CABINETS

- Broad range of pre-engineered configurations for networking equipment, switches and servers
- Horizontal and vertical cable management
- 4 different widths, 4 different depths and fully compatible accessories



SMART CABLE MANAGEMENT

VERTICAL AND HORIZONTAL MANAGERS

- Single- or double-sided models available
- Mounts on sides of or between 2- and 4-post open frame racks
- High capacity patch cord support and management
- Supports Cat 5e, 6A and fiber optic cables






SMART FASTENING AND FIXING

CAT HP J-HOOK SYSTEM

- Advanced, non-continuous pathway support solution
- One-person installation
- No grounding and bonding
- Multiple color options
- Fire rated



ROD LOCK

- Fast, easy and secure installations
- "Push-to-install" design
- Prefabricated (multi-level trapeze) assemblies
- Telescoping strut eliminates the need for cutting and preparing sections




SPEED LINK

- Universal overhead support system for time saving installation
- Complete systems for easy fastening to different building structures
- Unique push/pull keyless release enables easy adjustments
- Fire rated



SMART CABLE SUPPORT AND PATHWAYS


- Ceiling mounted and under floor configurations
- Easy access for maintenance
- Flexible line of components and accessories



SMART GROUNDING AND BONDING

GROUNDING AND BONDING

Full range of facility electrical protection products to protect data centers, network and other facilities



Work with Experts

TO DEPLOY YOUR SPECIFIED SOLUTION

SMART FACTORY / INDUSTRY 4.0

Today's "Connected Enterprise" networks need to support expanding voice, data and video applications on the factory floor and harsh environments. Industrial Networks & IoT deployments also require protection for edge-computing applications, such as industrial automation, intelligent lighting, security and safety systems.

nVent offers a broad range of industrial networking rack and enclosure solutions for protecting IT Equipment (ITE) on the factory floor. Options include integrated AC units and NEMA Type 1, 3R, 4, 4X, and 12 rated protection.



SMART COOLING SOLUTIONS

Maintaining high availability (uptime) at minimal operational costs remains a major challenge in today's data centers and networks. A significant portion of data center budgets includes energy consumption for IT Equipment and server cooling. In addition to traditional High-Performance Computing (HPC), AI-related compute-intensive applications have also increased the development of new designs for efficient cooling for data centers and edge computing. nVent offers a comprehensive range of standard and customized air, indirect and direct water cooling solutions.

Continuum of Cooling





PROFESSIONAL SERVICES

With a network of qualified field installation and repair technicians around the world, nVent offers unparalleled cooling service to quickly restore your system. Depend on us for local customer service, regional spare parts inventories and competitive standard warranties. Extended warranties and preventive maintenance are also available.

Europe

Straubenhardt, Germany	Tel: +49 7082 794 0
Betschdorf, France	Tel: +33 3 88 90 64 90
Warsaw, Poland	Tel: +48 22 209 98 35
Assago, Italy	Tel: +39 02 577 6151 224

North America

All locations	Tel: +1 763 422 2661
----------------------	----------------------

Middle East & India

Dubai, United Arab Emirates	Tel: +971 4 823 8666
Bengaluru, India	Tel: +91 80 6715 8900
Istanbul, Turkey	Tel: +90 541 3680941

Asia

Shanghai, China	Tel: +86 21 2412 6943
Qingdao, China	Tel: +86 523 8771 6101
Singapore	Tel: +65 6768 5800
Shin-Yokohama, Japan	Tel: +81 45 476 0271

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER



[nVent.com/DNS](https://www.nvent.com/DNS)