

## **PIVOTRACK**



## **INDUSTRY STANDARDS**

UL 2416 Listed; File Number E230874 Rated to 100 lbs. with a 4X safety factor

EIC 310-D

### **APPLICATION**

PIVOTRACK is used for wall mounting and securing 19-inch rack equipment for Telecommunication rooms and other locations. It provides an economical means to support remote 19-inch rack equipment. These open frame racks are ideal for high-density cabling applications while providing maximum access to equipment and cables. PIVOTRACK is ideal for IDFs (Intermediate Distribution Frames), remote 19-inch rack equipment, building automation, security and many other applications.

#### **FEATURES**

- Designed to accommodate all standard 19-inch rack equipment
- Easy, single-tool assembly reduces installation time and cost
- Central pivot in two-position mounting provides maximum versatility
- UL double lug ground holes provide easy adherence to local bonding and grounding codes
- Lanyard pin locks rack in increments of 15°, providing a stable position for cable and equipment installs
- Preassembled for fast, time-saving installation
- Temporary mounting bracket allows for rapid, single-person wall installation
- Smart packaging with hand carrying holes allows for easy transportation
- Cable tie down points, sized for up to 1-inch Velcro® straps, provided in horizontal and vertical positions in multiple locations
- Standard 24-inch deep offering to accommodate various applications
- Open design provides for maximum access to cables and equipment
- 19-inch rack fasteners (Phillips head, pilot point, black) 12-24, quantity 20, included

#### **SPECIFICATIONS**

- Wall section made of heavy gauge, formed, cold rolled steel construction
- Welded pivoting rack section made of formed, cold rolled steel
- Tapped 12-24 holes per EIA Universal pattern standards (1/4-5/8-5/8-1/4)

### **FINISH**

- Pretreated steel coated with RAL 9005 black textured, low-gloss polyester powder paint
- Mounting hardware is clear or black plate
- Rack 12-24 fasteners plated black

#### **LOAD RATING**

Static working load rating is 150 lbs. for all sizes.


## **ACCESSORIES**

Horizontal Cable Managers Blanking Panels Grounding kits Velcro Tie down straps PDUs Shelves

## **BULLETIN: DOFRW**

### Standard Product

		D	G	
Catalog Number	AxBxC in./mm	in./mm	in./mm	Rack Units
E19SWMC12U24	30.00 x 7.00 x 24.10	22.78	26	12
	762 x 178 x 612	578	660	
E19SWMC20U24	44.00 x 7.00 x 24.10	36.75	40	20
	1118 x 178 x 612	933	1016	



## **PIVOTRACK HARDWARE KIT**



Kit consists of (20) 12-24x.625 pilot point screws; (1) wall clip; and installation instructions.

## BULLETIN: DOFRW

Standard Product

Catalog Number	Descripton
EPKIT	PIVOTRACK hardware kit



# Notes