

## Basic Strip



### Single phase basicPDU

Input Rating : 20A, 208V  
 Outlet : 10A Rated C13 x 20  
 16A Rated C19 x 4  
 Inlet : 20A NEMA L6-20P plug  
 Cordset : 3 meter 12AWG cordset  
 Protection : 20A single pole hydraulic MCB x 1  
 Circuit Details : Output 16A max. C13 #1-20 + C19 #C1-C4

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

EMC Compliance : FCC Part 15 Subpart B  
 Safety Compliance : UL 60950-1:2007/R:2014-10  
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10  
 UL 62368-1:2014  
 CAN/CSA-C22.2 No. 62368-1:2014  
 UL 60730-1 Ed.5 (2016)  
 Environment Compliance : RoHS2 & REACH

Chassis Material : Steel  
 Chassis Color : Black

Product Dimension : 2.1 (W) x 3.1 (D) x 43.3 (H) inch  
 Net Weight : 9.7 lbs

Packing Dimension ( for 2 PDUs ) : 4.3 (W) x 10.6 (D) x 54.8 (H) inch  
 PDU Gross Weight ( for 2 PDUs ) : 25.7 lbs