



### Single phase monitored PDU

Input Rating : 30A, 208V  
 Outlet : 10A Rated C13 x 36  
 16A Rated C19 x 6  
 Inlet : 30A NEMA L6-30P plug  
 Cordset : 3 meter 10AWG cordset  
 Protection : 16A 1-pole hydraulic MCB x 2  
 Circuit Details : < **Circuit A** > Output 12A max. C13 # 1-18 + C19 # C1-C3  
 < **Circuit B** > Output 12A max. C13 # 19-36 + C19 # C4-C6

### Meter Features ( W monitored PDU )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
 Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
 Accuracy : ±1% Billing-grade  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : V2 / V3 via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

EMC Compliance : FCC Part 15 Subpart B certified  
 Safety Compliance : cTUVus Mark to UL 60950-1:2007/R:2014-10  
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10  
 UL 62368-1:2014  
 CAN/CSA-C22.2 No. 62368-1:2014  
 UL 60730-1 Ed.5 (2016)  
 Environment Compliance : RoHS2 & REACH

Chassis Material : Steel  
 Chassis Color : Black  
 Product Dimension : 2.1 (W) x 3.1 (D) x 67.9 (H) inch  
 Net Weight : 17.6 lbs

Packing dimension ( for 2 PDUs ) : 4.3 (W) x 10.6 (D) x 80.4 (H) inch  
 PDU gross weight ( for 2 PDUs ) : 39.6 lbs

### Mounting Method

