



unit : mm

### Single phase monitored PDU

Input Rating : 30A, 208V  
 Outlet : 10A rated C13 x12  
 Inlet : 30A NEMA L6-30P plug  
 Cordset : 3 meter UL 10AWG cordset  
 Protection : 16A single pole hydraulic MCB x2  
 Circuit Details : < **Circuit A** > Output 12A max. C 1 3 # 1 - 6  
 < **Circuit B** > Output 12A max. C13 #7-12

Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

### Meter Features ( W monitored PDU )

Local Display : Field replaceable 2.0" color LCD with touchscreen  
 Bank Measurement : Voltage ( V ), Current ( A ), energy ( kWh ) & power factor  
 Accuracy : ±1% Billing-grade  
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
 Cascade : Up to 16 PDU under single IP address via IP dongle  
 SNMP : V2 / V3 via IP dongle  
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : FCC Part 15 Subpart B certified  
 Safety Compliance : cTUVus Mark to UL60950-1:2007/R:2014-10  
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10  
 UL 62368-1:2014  
 CAN/CSA-C22.2 No. 62368-1:2014  
 UL 60730-1 Ed.5 (2016)

Environment Compliance : RoHS2 & REACH

Chassis Material : Steel  
 Chassis Color : Black  
 Product Dimension : 17.2 (W) x 7.1 (D) x 1.8 (H) inch  
 Net Weight : 13.6 lbs  
 Packing Dimension : 20.7 (W) x 11.4 (D) x 3.1 (H) inch  
 PDU Gross Weight : 14.7 lbs