



HOFFMAN ENCLOSURES, INC.
2100 Hoffman Way
Minneapolis, MN 55303-1745, USA
+1.763.421.2240 main

Declaration of Conformity

Issued by Manufacturer
Hoffman Enclosures, Inc.
2100 Hoffman Way, Anoka, Minnesota 55303-1745, U.S.A.
declare at our sole responsibility, that these devices are designed and constructed according to
the fundamental safety and health requirements.

Enclosure Models: APWK****H (Bulletin A80W)
Equipment Description: Hoffman Type 12 Hinged Window Kits
Enclosure Rating: CSA Type 12
Enclosure Certification: CSA C22.2 No. 14 - 13

PRODUCTS

CLASS 3211 07 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus
CLASS 3211 87 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - Certified to US
Standards

Hinged window kits, Series A-PWKXXXXXH, CSA Type 12, max size 30 in by 24 in.
Permanently mounted window kits, Series A-PWKXXXXXNF, CSA Types 4, 12, max size 37.5 in by 25.5 in,
Series A-PWKXXXXXNFSS, Type 4X, 4, 12, max size 31.5 in by 21.5 in.

Applicable Standards: CSA C22.2 No. 14 - 13 – Industrial Control Equipment
CAN/CSA C22.2 No. 94-M91 – Special Purpose Enclosures
ANSI/UL 50 (11th edition) – Enclosures for Electrical Equipment
ANSI/UL 508 (13th edition) – Industrial Control Equipment

Authorized by:

5/22/2020 (today's date)

Glen Kampa

Date

Senior Regulatory Engineer

Subject to Change Without Notice

DOC: CERT-00257-B



Certificate of Compliance

Certificate: 70076407 Master Contract: 151630 (042186_C_000)
Project: 70177560 Date Issued: 2018-04-12
Issued to: Hoffman Enclosures Inc.
 2100 Hoffman Way
 Anoka, Minnesota 55303-1745
 USA
 Attention: Glen Kampa

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.



Issued by: *Douglas Bramwell*
 Douglas Bramwell

PRODUCTS

CLASS 3211 07 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus
CLASS 3211 87 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - Certified to US Standards

Hinged window kits, Series A-PWKXXXXXH, CSA Type 12, max size 30 in by 24 in.
Permanently mounted window kits, Series A-PWKXXXXXNF, CSA Types 4, 12, max size 37.5 in by 25.5 in,
Series A-PWKXXXXXNFSS, Type 4X, 4, 12, max size 31.5 in by 21.5 in.

Notes:

1. For use only in Certified equipment where the acceptability of the combination is determined by Canadian Standards Association.
2. These devices are for mounting in enclosures having the same type environmental ratings.
3. Window kits, Series A-PWK53XXXXXNF and A-PWKXXXXXH may be provided with acrylic (Acrylite) (in lieu of polycarbonate Lexan) window, if shock hazard does not exist behind the observation opening.
4. "XXXXX" is catalogue designation denotes dimensions.



Certificate: 70076407

Project: 70177560

Master Contract: 151630

Date Issued: 2018-04-12

APPLICABLE REQUIREMENTS

CSA C22.2 No. 14-13	-Industrial Control Equipment
CAN/CSA-C22.2 No. 94-M91	-Special Purpose Enclosures
UL Std No.508, 17 th Ed	-Industrial Control Equipment
UL Std No. 50, 13 TH Ed	-Enclosures for Electrical Equipment