

nVent CADDY Sway Bracing Cable Swaging Tools and Cutters

For instruction on how to use your swaging tool or cutter, read through the manufacturers instruction that are enclosed with this sheet. See page two for tool/cable suitability.



CSB12SBHS
404461



CSB3346SB
402209



CSBBS121836
402534



SLWC
195853



CSBC48
402536

WARNING:

1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.
5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
6. All pipe supports, hangers, intermediate components and structural attachments must **ONLY** be used as described herein and are **NEVER** to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

TECHNICAL SUPPORT:
www.nVent.com

CFS430_K

1 OF 2

© 2010-2021 nVent All Rights Reserved

Global Part Number	Article Number	Description	Galvanized Cable		
			Red, #12, 3/32 in [2.4 mm]	White, #18, 1/8 in [3.2 mm]	Blue, #36, 3/16 in [4.8 mm]
CSB12SBHS	404461	Single Cavity Ratcheting Swage Tool	X		
CSB3346SB	402209	Five Cavity Hand Swage Tool	X	X	X
CSBBS121836	402534	Battery Powered Swage Tool	X	X	X
SLWC	195853	Wire Rope Cutter	X		
CSBC48	402536	Wire Rope Cutter	X	X	X

Note: For hand swaging tools, 2 swages are required for #12 and #18 size cables and 3 swages are required for #36 cables.

For battery powered swaging tool, 1 swage is required for #12 and #18 size cables, 2 swages are required for #36 size cable.