


# nVent CADDY All-in-One with Adjustable Mud Ring



## CONNECT AND PROTECT

### NVENT CADDY ALL-IN-ONE STUD-MOUNTED WITH ADJUSTABLE MUD RING



Material: Steel  
Finish: Pregalvanized  
Knockout Sizes: (8) 1/2", 3/4"; (3) 1/2"

- Adjustable mud ring accommodates various thicknesses of drywall
- Can be adjusted after the installation of drywall
- Box remains fixed in place when mud ring is removed
- Includes multiple knockouts on each side of the box
- Assemblies keyed for precise alignment when installed on both sides of a stud

Part Number	Gang	Ground Wire Included	Back Plate Pre-assembled	Box Volume	Drywall Thickness	Depth	Width	Window Height
A1SFV1G	1	Yes	Yes	32.8 in <sup>3</sup>	3/4" - 1 1/2"	3 5/8"	5 3/4"	5 1/8"
A1SFV1GS	1	Yes	Yes	32.8 in <sup>3</sup>	3/4" - 1 1/2"	2 1/2"	5 3/4"	5 1/8"
A1SFV2G	2	Yes	Yes	32.8 in <sup>3</sup>	5/8" - 1 1/2"	3 5/8"	5 3/4"	5 1/8"
A1SFV2GS	2	Yes	Yes	32.8 in <sup>3</sup>	5/8" - 1 1/2"	2 1/2"	5 3/4"	5 1/8"

Ground wire pigtail is 10".

### NVENT CADDY ALL-IN-ONE BETWEEN-STUD WITH ADJUSTABLE MUD RING



Material: Steel  
Finish: Pregalvanized  
Knockout Sizes (Single) Box: (8) 1/2", 3/4"; (3) 1/2"  
Knockout Sizes, (Multi) Box 1: (8) 1/2", 3/4"; (3) 1/2"  
Knockout Sizes, (Multi) Box 2: (5) 1/2", 3/4"; (1) 1/2"; (3) 1"

- Adjustable mud ring accommodates various thicknesses of drywall
- Comes with multiple boxes pre-assembled for side by side power and data applications
- Can be adjusted after the installation of drywall
- Box remains fixed in place when mud ring is removed
- Pre-bent tabs on support bracket help to quickly square assembly to stud
- Center marks provide easy height positioning
- Includes multiple knockouts on each side of the box

Part Number	Gang	Ground Wire Included		Box Volume	Drywall Thickness	Stud Spacing	Depth	Height	Window Height
		Box 1	Box 2						
<b>Single Box</b>									
A1BFV1GS	1	Yes		32.8 in <sup>3</sup>	3/4" - 1 1/2"	16" - 24"	2 1/2"	5 3/4"	4 1/8"
A1BFV1G	1	Yes		32.8 in <sup>3</sup>	3/4" - 1 1/2"	16" - 24"	3 5/8"	5 3/4"	4 1/8"
<b>Multi Box</b>									
A1BFV1GDV1NS	1	Yes	Yes	32.8 in <sup>3</sup>	3/4" - 1 1/2"	16" - 24"	2 1/2"	5 3/4"	4 1/8"
A1BFV1GDV1N	1	Yes	Yes	32.8 in <sup>3</sup>	3/4" - 1 1/2"	16" - 24"	3 5/8"	5 3/4"	4 1/8"
A1BFV1GFV1N	1	Yes	Yes	32.8 in <sup>3</sup>	3/4" - 1 1/2"	16" - 24"	3 5/8"	5 3/4"	4 1/8"

Ground wire pigtail is 10". 24" stud spacing requires use of three mounting screws. Use only with nVent CADDY All-in-One box assemblies.

## NVENT CADDY ALL-IN-ONE FLOOR-MOUNTED WITH ADJUSTABLE MUD RING



Material: Steel  
 Finish: Pregalvanized  
 EMT Conduit Size: 1/2"; 3/4"  
 MC/AC Cable Size: 14-2 to 12-3  
 Knockout Sizes: (8) 1/2", 3/4"; (3) 1/2"

- Preset to a finish height of 18" from the floor (adjustable to 12" or 15")
- Adjustable mud ring accommodates various thicknesses of drywall
- Can be adjusted after the installation of drywall
- Box remains fixed in place when mud ring is removed
- Integrated first means of support accepts conduit or MC/AC cable
- Accommodates additional nVent CADDY All-in-One box assemblies, support brackets and low-voltage mounting plates
- Includes multiple 1/2" and 3/4" knockouts on each side of the box

Part Number	Gang	Ground Wire Included	Box Volume	Drywall Thickness	Stud Depth	Height	Width	Depth
A1FFV1G	1	Yes	32.8 in <sup>3</sup>	3/4" - 1 1/2"	3 5/8"	22 3/16"	7 3/4"	2 11/16"
A1FFV2G	2	Yes	32.8 in <sup>3</sup>	5/8" - 1 1/2"	3 5/8"	22 3/16"	7 3/4"	2 11/16"

## ADJUSTABLE MUD RING



Material: Steel  
 Finish: Pregalvanized

- Adjustable mud ring accommodates various thicknesses of drywall
- Can be adjusted after the installation of drywall

Part Number	Box Size	Gang	Drywall Thickness
AMR1020SG	4	1	5/8" - 1 1/4"
AMR1224SG	4	1	3/4" - 1 1/2"
AMR1224RO	4	1	3/4" - 1 1/2"
AMR1024DG	4	2	5/8" - 1 1/2"
AMR1224TG	Multi Gang	3	3/4" - 1 1/2"
AMR1224SG41	4 11/16"	1	3/4" - 1 1/2"
AMR1024DG41	4 11/16"	2	5/8" - 1 1/2"

## PROTECTOR PLATE




- Universal protective cover protects electrical devices during drywall installation
- Gangable for multiple devices in any size box
- For toggle switch application use with PRPDH insert

Material: Steel  
 Finish: Pregalvanized

Part Number	Gang
PRP1G	1

## SWITCH PROTECTOR PLATE INSERT



- Insert used with PRP1G to protect toggle switch during drywall installation

Material: Steel  
 Finish: Pregalvanized

Part Number	Use With
PRPDH	PRP1G



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**