


Type T9 Special



Prior to making a connection, read and follow the full instruction sheet IPRNLBR, the Full instruction sheet IPP, full instruction sheet shipped with CADWELD® (IPX), and special instructions below.

1. Position cable on side of rail.
2. Position mold on cable so that end of cable end is directly under center of tap hole. This will be 1" [25.4 mm] from side of mold. Clamp mold to side of rail.
3. Pack opening around cable with ERICO mold sealer (ERICO part number T403) to prevent leakage.

WARNING:

1. ERICO products shall be installed and used only as indicated in ERICO product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative.
2. ERICO products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.