

FLEXIBAR ADVANCED VS FLEXIBAR STD TINNED CROSS REFERENCE TABLE

PRODUCT RETURNS WILL NOT BE ACCEPTED

ERIFLEX FLEXIBAR ADVANCED					
Article N°	PSF	Part N°	DESCRIPTION	Qty	UM
534000	LG	FADV2MTC8X6	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X6X0,5	4	pc
534001	LG	FADV2MTC3X9	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X9X0,8	4	pc
534002	LG	FADV2MTC6X9	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X9X0,8	4	pc
534003	LG	FADV2MTC9X9	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 9X9X0,8	4	pc
534004	LG	FADV2MTC3X13	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X13X0,5	4	pc
534005	LG	FADV2MTC6X13	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X13X0,5	4	pc
534006	LG	FADV2MTC2X15-5	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 2X15,5X0,8	4	pc
534007	LG	FADV2MTC4X15-5	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X15,5X0,8	4	pc
534008	LG	FADV2MTC6X15-5	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X15,5X0,8	4	pc
534009	LG	FADV2MTC10X15-5	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X15,5X0,8	4	pc
534010	LG	FADV2MTC2X20X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 2X20X1	3	pc
534011	LG	FADV2MTC3X20X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X20X1	3	pc
534012	LG	FADV2MTC4X20X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X20X1	3	pc
534013	LG	FADV2MTC5X20X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X20X1	3	pc
534014	LG	FADV2MTC6X20X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X20X1	3	pc
534015	LG	FADV2MTC10X20X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X20X1	3	pc
534016	LG	FADV2MTC2X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 2X24X1	3	pc
534017	LG	FADV2MTC3X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X24X1	3	pc
534018	LG	FADV2MTC4X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X24X1	3	pc
534019	LG	FADV2MTC5X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X24X1	3	pc
534020	LG	FADV2MTC6X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X24X1	3	pc
534021	LG	FADV2MTC8X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X24X1	3	pc
534022	LG	FADV2MTC10X24X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X24X1	3	pc
534023	LG	FADV2MTC2X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 2X32X1	2	pc
534024	LG	FADV2MTC3X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X32X1	2	pc
534025	LG	FADV2MTC4X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X32X1	2	pc
534026	LG	FADV2MTC5X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X32X1	2	pc
534027	LG	FADV2MTC6X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X32X1	2	pc

ERIFLEX FLEXIBAR STANDARD TINNED **DISCONTINUED**			
Article N°	PSF	Part N°	DESCRIPTION
505051	GO	FLEX2MTC3X9X0-8	ERIFLEX FLEXIBAR 2MTC 3X9X0.8
505052	GO	FLEX2MTC6X9X0-8	ERIFLEX FLEXIBAR 2MTC 6X9X0.8
505053	GO	FLEX2MTC3X13	ERIFLEX FLEXIBAR 2MTC 3X13X0.5
505054	GO	FLEX2MTC6X13	ERIFLEX FLEXIBAR 2MTC 6X13X0.5
505059	GO	FLEX2MTC2X15-5	ERIFLEX FLEXIBAR 2MTC 2X15.5X0.8
505055	GO	FLEX2MTC4X16	ERIFLEX FLEXIBAR 2MTC 4X15.5X0.8
505056	GO	FLEX2MTC6X16	ERIFLEX FLEXIBAR 2MTC 6X15.5X0.8
505501	GO	FLEX3MTC2X20X1	ERIFLEX FLEXIBAR 3MTC 2X20X1
505502	GO	FLEX3MTC3X20X1	ERIFLEX FLEXIBAR 3MTC 3X20X1
505503	GO	FLEX3MTC4X20X1	ERIFLEX FLEXIBAR 3MTC 4X20X1
505504	GO	FLEX3MTC5X20X1	ERIFLEX FLEXIBAR 3MTC 5X20X1
505505	GO	FLEX3MTC6X20X1	ERIFLEX FLEXIBAR 3MTC 6X20X1
505506	GO	FLEX3MTC2X24X1	ERIFLEX FLEXIBAR 3MTC 2X24X1
505507	GO	FLEX3MTC3X24X1	ERIFLEX FLEXIBAR 3MTC 3X24X1
505508	GO	FLEX3MTC4X24X1	ERIFLEX FLEXIBAR 3MTC 4X24X1
505509	GO	FLEX3MTC5X24X1	ERIFLEX FLEXIBAR 3MTC 5X24X1
505510	GO	FLEX3MTC6X24X1	ERIFLEX FLEXIBAR 3MTC 6X24X1
505511	GO	FLEX3MTC8X24X1	ERIFLEX FLEXIBAR 3MTC 8X24X1
505512	GO	FLEX3MTC10X24X1	ERIFLEX FLEXIBAR 3MTC 10X24X1
505513	GO	FLEX3MTC2X32X1	ERIFLEX FLEXIBAR 3MTC 2X32X1
505514	GO	FLEX3MTC3X32X1	ERIFLEX FLEXIBAR 3MTC 3X32X1
505515	GO	FLEX3MTC4X32X1	ERIFLEX FLEXIBAR 3MTC 4X32X1
505516	GO	FLEX3MTC5X32X1	ERIFLEX FLEXIBAR 3MTC 5X32X1
505517	GO	FLEX3MTC6X32X1	ERIFLEX FLEXIBAR 3MTC 6X32X1

FLEXIBAR ADVANCED VS FLEXIBAR STD TINNED CROSS REFERENCE TABLE (end)

ERIFLEX FLEXIBAR ADVANCED					
Article N°	PSF	Part N°	DESCRIPTION	Qty	UM
534028	LG	FADV2MTC8X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X32X1	2	pc
534029	LG	FADV2MTC10X32X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X32X1	2	pc
534030	LG	FADV2MTC2X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 2X40X1	2	pc
534031	LG	FADV2MTC3X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X40X1	2	pc
534032	LG	FADV2MTC4X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X40X1	2	pc
534033	LG	FADV2MTC5X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X40X1	2	pc
534034	LG	FADV2MTC6X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X40X1	2	pc
534035	LG	FADV2MTC8X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X40X1	2	pc
534036	LG	FADV2MTC10X40X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X40X1	2	pc
534037	LG	FADV2MTC3X50X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 3X50X1	1	pc
534038	LG	FADV2MTC4X50X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X50X1	1	pc
534039	LG	FADV2MTC5X50X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X50X1	1	pc
534040	LG	FADV2MTC6X50X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X50X1	1	pc
534041	LG	FADV2MTC8X50X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X50X1	1	pc
534042	LG	FADV2MTC10X50X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X50X1	1	pc
534044	LG	FADV2MTC4X63X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X63X1	1	pc
534045	LG	FADV2MTC5X63X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X63X1	1	pc
534046	LG	FADV2MTC6X63X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X63X1	1	pc
534047	LG	FADV2MTC8X63X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X63X1	1	pc
534048	LG	FADV2MTC10X63X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X63X1	1	pc
534049	LG	FADV2MTC4X80X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 4X80X1	1	pc
534050	LG	FADV2MTC5X80X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X80X1	1	pc
534051	LG	FADV2MTC6X80X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X80X1	1	pc
534052	LG	FADV2MTC8X80X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X80X1	1	pc
534053	LG	FADV2MTC10X80X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X80X1	1	pc
534055	LG	FADV2MTC5X100X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 5X100X1	1	pc
534056	LG	FADV2MTC6X100X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 6X100X1	1	pc
534057	LG	FADV2MTC8X100X1	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 8X100X1	1	pc
534058	LG	FADV2MTC10X100	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X100X1	1	pc
534059	LG	FADV2MTC12X100	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 12X100X1	1	pc
534060	LG	FADV2MTC10X120	ERIFLEX FLEXIBAR Advanced 2 m Tinned Copper 10X120X1	1	pc

ERIFLEX FLEXIBAR STANDARD TINNED			
Article N°	PSF	Part N°	DESCRIPTION
505518	GO	FLEX3MTC8X32X1	ERIFLEX FLEXIBAR 3MTC 8X32X1
505519	GO	FLEX3MTC10X32X1	ERIFLEX FLEXIBAR 3MTC 10X32X1
505521	GO	FLEX3MTC3X40X1	ERIFLEX FLEXIBAR 3MTC 3X40X1
505522	GO	FLEX3MTC4X40X1	ERIFLEX FLEXIBAR 3MTC 4X40X1
505523	GO	FLEX3MTC5X40X1	ERIFLEX FLEXIBAR 3MTC 5X40X1
505524	GO	FLEX3MTC6X40X1	ERIFLEX FLEXIBAR 3MTC 6X40X1
505525	GO	FLEX3MTC8X40X1	ERIFLEX FLEXIBAR 3MTC 8X40X1
505526	GO	FLEX3MTC10X40X1	ERIFLEX FLEXIBAR 3MTC 10X40X1
505527	GO	FLEX3MTC3X50X1	ERIFLEX FLEXIBAR 3MTC 3X50X1
505528	GO	FLEX3MTC4X50X1	ERIFLEX FLEXIBAR 3MTC 4X50X1
505529	GO	FLEX3MTC5X50X1	ERIFLEX FLEXIBAR 3MTC 5X50X1
505530	GO	FLEX3MTC6X50X1	ERIFLEX FLEXIBAR 3MTC 6X50X1
505531	GO	FLEX3MTC8X50X1	ERIFLEX FLEXIBAR 3MTC 8X50X1
505532	GO	FLEX3MTC10X50X1	ERIFLEX FLEXIBAR 3MTC 10X50X1
505534	GO	FLEX3MTC4X63X1	ERIFLEX FLEXIBAR 3MTC 4X63X1
505535	GO	FLEX3MTC5X63X1	ERIFLEX FLEXIBAR 3MTC 5X63X1
505536	GO	FLEX3MTC6X63X1	ERIFLEX FLEXIBAR 3MTC 6X63X1
505537	GO	FLEX3MTC8X63X1	ERIFLEX FLEXIBAR 3MTC 8X63X1
505538	GO	FLEX3MTC10X63X1	ERIFLEX FLEXIBAR 3MTC 10X63X1
505540	GO	FLEX3MTC4X80X1	ERIFLEX FLEXIBAR 3MTC 4X80X1
505541	GO	FLEX3MTC5X80X1	ERIFLEX FLEXIBAR 3MTC 5X80X1
505542	GO	FLEX3MTC6X80X1	ERIFLEX FLEXIBAR 3MTC 6X80X1
505543	GO	FLEX3MTC8X80X1	ERIFLEX FLEXIBAR 3MTC 8X80X1
505544	GO	FLEX3MTC10X80X1	ERIFLEX FLEXIBAR 3MTC 10X80X1
505546	GO	FLEX3MTC5X100X1	ERIFLEX FLEXIBAR 3MTC 5X100X1
505547	GO	FLEX3MTC6X100X1	ERIFLEX FLEXIBAR 3MTC 6X100X1
505548	GO	FLEX3MTC8X100X1	ERIFLEX FLEXIBAR 3MTC 8X100X1
505549	GO	FLEX3MTC10X100	ERIFLEX FLEXIBAR 3MTC 10X100X1
505550	GO	FLEX3MTC12X100	ERIFLEX FLEXIBAR 3MTC 12X100X1