

Quick Strut Nut with Stud

FEATURES GUIDE

EASE OF USE FEATURES

Ready to use out of the box with no loose hardware

SAFETY FEATURES

One-piece design limits the likelihood of dropped parts

STRENGTH FEATURES

Threaded rod is locked in strut nut to avoid rotation

The spring-loaded connection locks the part in the channel and allows for easy repositioning

4 mm-thick square provides strength to support all common pipe sizes up to DN200

The square top plate allows for easy handling, even when wearing gloves

Assembled with a standard strut nut to ensure a high load rating

Easily preassembled with pipe support off-site, saving installation time

Available in two sizes of threaded rod [M8 and M10]

Compatible with standard strut sizes

The color of the line corresponds to the larger goal of each feature:

EASE OF USE FEATURES

SAFETY FEATURES

STRENGTH FEATURES

Electrogalvanized coating provides a durable protection against corrosion

Safety factor of 3:1 on static loads



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER