


# RTD3CS and RTD10CS

## CONNECT AND PROTECT

### RTD temperature sensors for temperature measurement up to 400°F (204°C)

#### PRODUCT OVERVIEW



The nVent RAYCHEM RTD3CS and RTD10CS are three-wire platinum RTD (resistance temperature detectors) typically used with monitoring and control systems such as the nVent RAYCHEM 910 controller when accurate temperature control is required.

The RTD3CS and RTD10CS can be installed directly to the controller using the supplied 1/2" conduit fitting or to an RTD junction box where RTD extension wire is used.

#### SPECIFICATIONS

##### Sensor

Housing	316 stainless steel
Dimensions	3-in (76 mm) length 3/16-in (8 mm) diameter
Sensing area	1-1/2 in (38 mm)
Accuracy	±1°F (0.5°C) at 32°F (0°C)
Range	-76°F to 400°F (-60°C to 204°C)
Resistance	100 ohms at 0°C $\alpha = 0.00385$ ohms/ohm/°C

##### Extension wires

Wire size (each of three)	20 AWG, stranded tinned copper <b>Note:</b> The length of RTD extension wires is determined by the wire gauge used. To reduce the likelihood that electrical noise will affect temperature measurement, keep RTD extension wires as short as possible. Use shielded instrument cable such as nVent RAYCHEM MONI-RTD-WIRE (22 AWG, PVC insulation, -30°F to 140°F, -20°C to 60°C) or Belden 83553 (22 AWG, FEP insulation, -95°F to 395°F, -70°C to 200°C).
Wire insulation rating	300 V
Length	RTD3CS: 3-ft (0.3 m) flexible armor, 18-in (457 mm) lead wire RTD10CS: 10-ft (3 m) flexible armor, 18-in (457 mm) lead wire
Outer shield	Stainless steel flexible armor (not suitable for underground applications)
Maximum exposure temperature	400°F (204°C)
Conduit bushing	1/2-in (12.7 mm) NPT

#### ADDITIONAL MATERIALS REQUIRED

AT-180 aluminum tape

#### APPROVALS

Approvals associated with control device. Not to be used in Division 1 areas.

**North America**

Tel +1.800.545.6258  
Fax +1.800.527.5703  
thermal.info@nVent.com

**Europe, Middle East, Africa**

Tel +32.16.213.511  
Fax +32.16.213.604  
thermal.info@nVent.com

**Asia Pacific**

Tel +86.21.2412.1688  
Fax +86.21.5426.3167  
cn.thermal.info@nVent.com

**Latin America**

Tel +1.713.868.4800  
Fax +1.713.868.2333  
thermal.info@nVent.com



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**