Varistar
Containment

nVent

SCHROFF

Cabinets – VARISTAR containment

01012006

THE SCHROFF CONTAINMENT SYSTEM LETS YOU CREATE CONTAINMENT INSTALLATIONS WITHOUT PROBLEMS. INCREASE EFFICIENCY AND CUT ENERGY COSTS

- Consistent separation of cold and hot air
- Overpressure in the containment: Blow-in temperature of air conditioner is almost the same as the temperature in front of the servers
- No temperature layering in front of the 19" plane inside the containment
- No subcooling: possibilities to optimize temperature in data centres
- Higher packing density per cabinet is possible with the same climate control elements
- Low investment with short ROI - no maintenance costs

Cold aisle containment

Cabinets – VARISTAR containment

OVERVIEW

CONTAINMENT OF VARISTAR CABINETS

- **Modular standard components enable flexible adaptation to the requirements of your IT**
- **Base system simple to combine and modify**
- **Minimal investment risk thanks to completely matched climate control system**
- **Short implementation time with minimum outlay**

VARISTAR CONTAINMENT SYSTEM

- Preconfigured containment solution from modular standard components (consisting of 6 Varistar server cabinets, RAL 7021, height 2000 mm, width 800 mm, depth 1200 mm) including containment components; containment aisle width 1200 mm)
- Simple to expand or to use as the configuration basis for your individual containment solution
- Can be delivered in 10 working days

01014007

DOORS

- Standard solutions for 2000 mm and 2200 mm high cabinets
- Swing doors
- Sliding doors
  - Mechanical
  - Electronic

01012073

TOP COVERS

- Standard solutions for aisle width 1200 mm
- For 600 mm and 800 mm wide cabinets
- Integration of cabinets with other dimensions (heights)
- Free aisle height can be raised by 84 mm

01012074

AIR PARTITIONING

- For server and network cabinets
- For cabinets with different widths and recessed 19" planes
- Solid covers with cable ducting or cable routing (cable fingers, cable channels)
- Halogen-free gasketing UL 94 HF-1

01012055

SERVICEPLUS
e.g. set-up service and commissioning
e.g. custom modifications and developments
e.g. free combination of components

Cabinets – VARISTAR containment

VARISTAR CONTAINMENT SYSTEMS

01014007

01012073

Sliding containment door, mechanical, touch

01012070

Swing containment door

- Preconfigured containment solutions from modular standard components
- Simple to expand or to use as the configuration basis for your individual containment solution
- Consists of 6 Varistar server cabinets (height 2000 mm, width 800 mm, depth 1200 mm) including containment components
- Containment aisle width 1200 mm, all components in RAL 7021
- Can be delivered in 10 working days

DELIVERY INCLUDES

Item	Qty	Description
1	6	Welded basic frame, Slim-Line, St profile, zinc-plated, powder-coated, RAL 7021
2	24	Adjustable foot
3	6	Flat top cover, raised, St, RAL 7021, cutouts for brush strip mounting
4	12	Brush strip for cable entry to flat top cover
5	6	Front door, St, RAL 7021, with 180° hinges and perforation, 3-point locking and lever handle
6	6	Rear door, double door, St, RAL 7021, with 180° hinges and perforation, 3-point locking and lever handle
7	24	Cross member, RAL 7021, to accept 19" panel/slide mounts
8	24	19" panel/slide mounts, RAL 7021, mounted at 75 mm intervals
9	12	Air baffle, St, RAL 7021, with brush strip for cable ducting
10	24	Central C rail for lateral cable routing in cabinet
11	48	Steel cable bracket
12	4	Side panel, screw-fixed, for aisle closure, St, RAL 7021
13	1	Sliding containment doors, mechanical, Al extruded frame, 10 mm laminated safety glass, sliding mechanism and rail, fixing materials kit
14	1	Swing containment doors, St frame, 1.5 mm, with 6 mm single pane safety glass and 180° hinges
15	1	Top containment covers, frame St, 2 mm, RAL 7021, 7 mm laminated safety glass, length 1200 mm
16	6	Fixing materials for top cover universal profile
17	2	Top cover universal profile, Al, length 2400 mm, RAL 7021
18	4	Side-by-side mounting kit for cabinets
19	1	Containment gasketing kit
20	1	Separator for adjustable cabinet foot

ORDER INFORMATION

Description	Part no.
Varistar Containment Systems	10130-250

Cabinets – VARISTAR containment

SWING DOORS

01012070

Accessories

01012068

Door cover mask

01012060

Lock

- Suitable for 2000 and 2200 mm high cabinets
- Double doors suitable for an aisle width of 1200 mm
- 2 colours
  - Black grey (RAL 7021)
  - Light grey (RAL 7035)

DELIVERY COMPRISES

Item	Qty	Description
1	2	Frame St, 1.5 mm; with single pane safety glass 6 mm and 180° hinge, 2-point magnetic locking on main door, bolt on side door to lock into the floor
2	1	Fixing material kit (for cabinet side)

ORDER INFORMATION

| Description	Colour	Part no.
Swing doors	RAL 7021	21130-583
Swing doors	RAL 7035	22130-583
Accessories		
Door locking PU 1 pieces		23130-437
Door cover mask for unequal aisle heights		**Page 1.216**

NOTE

- Please order suitable door cover masks (above the door) separately
- Optional lever handle with lock on request

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 5

Cabinets – VARISTAR containment

SLIDING DOOR, MECHANICAL, TOUCH VARIANT

01012073

Accessories

01012067

Door cover mask

01012059

Assembly kit

- Suitable for 2000 and 2200 mm high cabinets
- Doors open symmetrically (both wings open at same time); door catch with magnet (door stays open); closes automatically when lightly tapped
- Double doors suitable for an aisle width of 1200 mm
- Colour black grey (RAL 7021)

DELIVERY COMPRISES

Item	Qty	Description
1	2	Sliding door, frame Al extrusion; laminated safety glass 10 mm, sliding gear
2	1	Slide rail with front trim
3	1	Fixing material kit (for cabinet side)

ORDER INFORMATION

Description	Part no.
Sliding door, mechanical, Touch variant version	21130-060
Accessories	
Reed contact 1 piece	60130-065
Door seal cover for various aisle heights	**Page 1.217**

NOTE

- Please order suitable door cover maskSs (above the door) separately

Cabinets – VARISTAR containment

SLIDING DOOR, ELECTRONIC

01012072

01010066

Optional door opening with motion sensor

Accessories

01012069

Door cover mask

01012059

Assembly kit

- Suitable for 2000 and 2200 mm high cabinets
- Door is opened/closed using a button (outside and inside); manually in case of power failure
- Double doors suitable for an aisle width of 1200 mm
- Colour black grey (RAL 7021)
- Optional door activation with motion sensor or operator unit with access control

DELIVERY COMPRISES

Item	Qty	Description
1	2	Sliding door, frame Al extrusion; laminated safety glass 10 mm, door sliding gear, connector cable and button to operate door
2	1	Slide rail with front trim
3	1	Fixing material kit (for cabinet side)

ORDER INFORMATION

| Description	Part no.
Sliding door, electronic	21130-073
Accessories	
Reed contact 1 piece	60130-065
Battery pack 1 piece	60130-066
Motion detector 1 piece	60130-067
Door seal cover for various aisle heights	**Page 1.218**

NOTE

- Please order suitable door cover masks (above the door) separately
- An assembly kit is required for cabinet height 2200 mm with base/plinth, please order separately
- The door system must be maintained and inspected regularly

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 7

Cabinets – VARISTAR containment

TOP COVER ELEMENTS

01008024

01012074

- Suitable for an aisle width of 1200 mm
- Top cover with safety glass (VSG)
- For cabinet widths 600 and 800 mm
- A top cover profile can raise the aisle height by 84 mm; please order separately
- Top cover can be removed from inside (allows access to lighting and facilitates maintenance works)

DELIVERY COMPRISES

Item	Qty	Description
1	1	Frame St, 2 mm, RAL 7021; safety glass (VSG) 7 mm, length 1200 mm
2	1	Fixing material kit

ORDER INFORMATION

Description	For cabinet width mm	Part no.
Top cover elements	600	21130-588
Top cover elements	800	21130-589
Accessories		
Top cover profile Length 2400 mm, PU 2 pieces		21130-594
Assembly kit bracket for top cover raising profile, PU 6 pieces		23130-433

NOTE

- Where a mechanical sliding door is used, the top cover directly beside the door must be 100 mm narrower, see page 1.205

UNIVERSAL PROFILE TO RAISE TOP COVER

01012051

Application with raised top covers

01012052

Accessory: Assembly kit to mount universal top cover profile

- The top cover elements can be raised by 84 mm using a profile
- Integration of cabinets with other dimensions
- The profile has a T-groove on the inside that allows lamps, sensors, etc, to be mounted easily

DELIVERY COMPRISES

Item	Qty	Description
1	2	Al extrusion, RAL 7021, length 2400 mm

ORDER INFORMATION

Description	Part no.
Universal top cover profile, height 84 mm	21130-594
Accessories	
Assembly kit Bracket for universal top cover profile, PU 6 pieces	23130-433

NOTE

- To mount a profile, an assembly kit (2 pieces) is required; please order separately

Cabinets – VARISTAR containment

AUTOMATIC ENCLOSURE TOP COVERS

01017054

01017053

- Automatic containment top covers open automatically in the event of fire so that the sprinkler systems installed above the containment top cover can put out the fire. In normal operation, the top covers are kept closed by electromagnets and open when the floating contact of the fire detection system is opened
- Suitable for an aisle width of 1200 mm
- For cabinet widths of 600 or 800 mm
- Top cover with safety glass, 7 mm
- With the universal top cover profile, the aisle height can be increased by 84 mm; please order separately
- The top cover can be removed from the inside. When opened, the top cover provides access to lighting and sprinkler systems above the containment system for maintenance work
- Please order the control unit, which can be used to control up to 12 automatic top covers, separately
- A 24 V_{DC} power supply unit is required to operate the system. Please order separately

DELIVERY INCLUDES

Item	Qty.	Description
1	1	Frame, St, 2 mm, RAL 7021; 7 mm laminated safety glass, length 1200 mm, electromagnet with 1200 mm connection cable
2	1	T-shaped connecting plug
3	1	Fixing materials kit

ORDER INFORMATION

| Description	Part no.
Automatic containment top cover, width 600 mm	21130-592
Automatic containment top cover, width 800 mm	21130-593
Accessories	
Raised top cover Length 2400 mm, PU 2 pieces	21130-594
Assembly kit Bracket for universal top cover profile, PU 6 pieces	23130-433
Control unit for automatic top covers 1 set	23130-205
Power supply for control unit For power distribution of up to 12 automatic top covers, input 100 to 240 V_{AC}, output: 24 V_{DC}, 40 W, 1 piece	23130-227
Connecting/extension cable, 1 m	23130-206
Connecting/extension cable, 2 m	23130-207
Connecting/extension cable, 5 m	23130-226

CONTROL UNIT FOR AUTOMATIC TOP COVERS

01017002

- Control unit for up to 12 automatic top covers
- Inputs:
  - External 24 V_{DC} power supply unit required, please order separately
  - 2 floating contacts for connecting to a fire detection system and another opening/test button
- Output: 24 V_{DC} connection for the control and voltage supply of up to 12 automatic enclosure top covers, which can be connected in series

ORDER INFORMATION

Description	Part no.
Control unit for automatic top covers	23130-205

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 9

ADAPTORS FOR CABLE ROUTING

01012075

01012076

Mounting bracket for cable route adaptor

- Suitable for VARISTAR cabinets and all common cable panel systems

DELIVERY COMPRISES

Item	Qty	Description
1	2	St profile, RAL 7021

ORDER INFORMATION

| Description	For cabinet depth mm	Part no.
Cable route adaptor	1000	**21130-596**
Cable route adaptor	1200	21130-597
Accessories		
Mounting bracket for cable route adaptor Bracket, St, PU 2 pieces		21130-598

NOTE

- Mounting bracket for cable route adaptor is required for containment without universal top cover profile

Cabinets – VARISTAR containment

COVERS

Covers for 800 mm wide cabinets with adapter bracket for reduced width

Covers solid, width 800 mm

Cover with lateral cut-outs

Cover with cable finger/ cable channel

Covers for 800 mm wide cabinets with cross member

Covers, width 800 mm

Cover with lateral cut-outs

- All around the front, covers prevent unwanted air short-circuits, i.e. the mixture of warm exhaust air with cold inbound air
- For cabinet width 600 or 800 mm, for cabinet height 42 or 47 U
- Versions for installation with adapter bracket for reduced width or cross member
  - Solid covers
  - Covers for 800 mm wide cabinets with cut-outs for cable routing
  - Covers with vertical cable fingers for 800 mm wide cabinets
  - Cable routing with cable channel (hinged cover at front) for 800 m wide cabinets
- Suitable divider plates are available for 19" planes mounted with recess (70, 145, 220 mm)
- Network and server cabinets can be arranged side by side
- Gaskets, UL 94 HF-1, -20 °C … 100° C

DELIVERY COMPRISES

| Item	Qty	Description
1a	2	Cover, St, 1 mm, RAL 7021, left/right (at 600 mm width only gaskets instead of covers)
2	1	Cover, top, St, 1 mm, RAL 7021
3	1	Cover, bottom, St, 1 mm, RAL 7021
4	1	Fixing material kit, gaskets, user manual

ORDER INFORMATION

Height		Covers for front air separation	For 600 mm wide cabinets	For 800 mm wide cabinets with adapter bracket for reduced width				For 800 mm wide cabinets with cross member	
				Solid cover	Cover with lateral cut-outs for cables	Cover with cable fingers	Cover with cable panels	Solid cover	Cover with lateral cut-outs for cables
U	mm		Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Part No.
42	2000	for 70 mm recessed 19" plane	**21130-624**	21130-627	21130-629	–	–	23130-550	23130-558
42	2000	for 145 mm recessed 19" plane	21130-618	21130-631	21130-620	–	–	23130-550	23130-558
42	2000	for 220 mm recessed 19" plane	21130-622	21130-633	21130-623	21130-636	21130-638	23130-550	23130-558
47	2200	for 70 mm recessed 19" plane	**21130-625**	21130-628	21130-630	–	–	23130-551	23130-559
47	2200	for 145 mm recessed 19" plane	21130-619	21130-632	21130-621	–	–	23130-551	23130-559
47	2200	for 220 mm recessed 19" plane	21130-626	21130-634	21130-635	21130-637	21130-639	23130-551	23130-559

Accessories

Lateral 19" baffle plates for 42 U cabinets, for lateral termination in depth of 70 mm, PU 1 piece	21130-640
Lateral 19" baffle plates for 42 U cabinets, for lateral termination in depth of 145 mm, PU 1 piece	21130-642
Lateral 19" baffle plates for 47 U cabinets, for lateral termination in depth of 70 mm, PU 1 piece	21130-641
Lateral 19" baffle plates for 47 U cabinets, for lateral termination in depth of 145 mm, PU 1 piece	21130-643
Brush strip for closing the open cable through-ducting opening, 1 U, black, PU 6 pieces	23130-153
Clip-on 19" plastic front panels to close the open cable through-ducting opening of the lateral cladding parts , 1 U, black, PU 10 pieces	**D19BPT1RU**

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 11

BASIC KIT FOR SIDE-TO-SIDE-COOLED SWITCHES

01013067

- Basic kit to divide the 19" plane in the front part of the cabinet and to accept side trims for switches
- For 800 mm wide VARISTAR cabinets
- with 145 mm recessed 19" plane
- Right front bezel with 5 x air inlets; air inlets that are not required can be closed with easy-to-cut gasketing material
- Left front bezel for back-to-back cabling with 3 x 19"/1 U cut-outs (please order brush strips and filler panels separately)
- Kit can also be retrofitted to cabinets already installed in rows

DELIVERY INCLUDES

Item	Qty	Description
1	2	Front frame, St, 1 mm, RAL 7021 (for top and bottom)
2	1	Cover, left, St, 1 mm, RAL 7021 (3 openings)
3	1	Cover, right, St, 1 mm, RAL 7021 (5 openings)
4	1	Base, St, 1 mm, AlZn, for Cisco side trim
5	1	Top cover, St, 1 mm, AlZn, for Cisco side trim
6	6	Gasketing (can be cut as required for air inlets)
7	1	Fixing materials kit, gasketing, user manual

ORDER INFORMATION

For cabinet height		For cabinet width	Part no.
U	mm	mm	
42	2000	800	21130-646
47	2200	800	21130-647
Accessories			
Side trims for Cisco switches for Cisco Switch 4503, side trim AlZn, 1 mm, 1 kit			23130-490
Side trims for Cisco switches for Cisco Switch 4506, side trim AlZn, 1 mm, 1 kit			23130-491
Side trims for Cisco switches for Cisco Switch 4507, side trim AlZn, 1 mm, 1 kit			23130-492
Side trims for Cisco switches for Cisco Switch 4510, side trim AlZn, 1 mm, 1 kit			23130-493
Side trims for Cisco switches for Cisco Switch 6506, side trim AlZn, 1 mm, 1 kit			23130-494
Side trims for Cisco switches for Cisco Switch 6509, side trim AlZn, 1 mm, 1 kit			23130-495
Side trims for Cisco switches for Cisco Switch 6510, side trim AlZn, 1 mm, 1 kit			23130-496
Clip-on 19" plastic front panels to close the open cable through-ducting opening of the lateral cladding parts 1 U, black, PU 10 pieces			**D19BPT1RU**
Brush strip for closing the open cable through-ducting opening 1 U, black, PU 6 pieces			23130-153

Cisco switches side trims

01013066

01013060

19" plastic front panels, brush strips to close cable ducting openings

NOTE

- Please order appropriate quantity and suitable Cisco switch side trims separately
- Cover for lateral cable through-ducting openings (please order brush strip and 19" front panel separately)

Cabinets – VARISTAR containment

SEPARATING WALLS

- Where cabinets are arranged in rows the separating wall replaces the cabinet side wall
- Mounts laterally, prevents unauthorised access
- For cabinet height 42 or 47 U and cabinet depth 1000 mm or 1200 mm

DELIVERY COMPRISES

Item	Qty	Description
1	1	Separating wall, St, 1 mm, finish AlZn
2	1	Fixing material kit, user manual

ORDER INFORMATION

For cabinet height U	For cabinet depth mm	Part no.
42	1000	23130-480
42	1200	23130-481
47	1000	23130-484
47	1200	23130-485

01012058

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 13

Vertical gasket 01012081

Horizontal gasket 01012082

- Gasketing kits to seal front against air short-circuits

DELIVERY COMPRISES

Item	Qty	Description
1	1	Gasket, halogen-free
2	1	User manual

ORDER INFORMATION

Description	Length mm	Part no.
Vertical gasket for vertical sealing between 10 cabinets	3000	23130-475
Horizontal gasket for two 600 mm wide cabinets with adjustable feet	1200	23130-477
Horizontal gasket for two 800 mm wide cabinets with adjustable feet	1600	23130-478

Cabinets – Varistar ServicePLUS containment

CONFIGURATION AID FOR AISLE CONTAINMENT

- For cabinet rows
  - Cabinet height 2000 and 2200 mm
  - Aisle width 1200 mm
  - Cabinet width 600 mm and 800 mm
- Colour RAL 7021, swing door also in RAL 7035
- Configure your containment system from individual components
- Once you have selected the desires cabinet containment height, the row number (first column of the configuration tables) guides you through all subsequent configutations pages that apply to these dimensions (see example below)
- Assembly on request

01012065

### Example 6 cabinet containment cells (here: row 6)

| Qty	Description	Order no.
6	Side-to-side cabinet, 47 U, 2200 mm high, 800 mm wide, 1200 mm deep, with front and rear door, RAL 7021, 1 piece (see chapter VARISTAR data/network systems)	10130-233
2	Side panel screw fixed, height 47 U - 2200 mm, for cabinet depth 1200 mm, RAL 7021, PU 2 pieces (see chapter VARISTAR data/network systems)	22130-537
1	Sliding door, mechanical, for cabinet height 2200 mm, aisle height 2102 mm, with adjustable foot + top cover raising element, 1 piece	21130-060
1	Door cover mask to equalize aisle height, 1 piece	21130-612
3	Top cover, for cabinet width 800 mm, aisle width 1200 mm, 1 piece	21130-589
1	Universal top cover profile, length 2400 mm, height 84 mm, PU 2 pieces	21130-594
1	Assembly kit for universal top cover profile, PU 6 pieces	23130-433
5	Cover, for lateral termination, 70 mm recessed, PU 1 kit	21130-638
5	Cover with lateral cutouts, by 145 mm recessed 19" plane, PU 1 kit	21130-632
2	Cover for lateral termination, depth-offset 70 mm, 1 piece	21130-643
..	....	....

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 15

SWING DOORS

ORDER INFORMATION

| | | | | Swing door | | | |
				RAL 7021	RAL 7035	Cover	Door locking
				01012064	01012063	01012068	01012060
				Frame, St, with single pane safety glass 6 mm and 180° hinge, 3-point loking and lever handle (please order lock separately), door cover mask to equalise aisle height, 1 piece		St, 1.5 mm, RAL 7021; cover to equalise aisle height	Door locking mechanism
No.	For cabinet height H U / mm	Aisle height (lower edge) mm	Raising elements	PU 2 pieces	1 piece	1 piece	1 piece
1	42 / 2000	2018	Adjustable feet	21130-583	22130-583	–	23130-437
2		2102	Adjustable feet + raised top cover				
3		2108	Base/plinth				
4		2192	Base/plinth + raised top cover				
5	47 / 2200	2218	Adjustable feet	21130-583	22130-583	21130-611	23130-437
6		2302	Adjustable feet + raised top cover			21130-612	
7		2308	Base/plinth			21130-612	
8		2392	Base/plinth + raised top cover			21130-613	

ORDER INFORMATION

				Hand operated sliding door, touch		
				RAL 7021	Cover	Reed contact

01012062

01012062

01012067

01015001

Sliding door, frame St, with single pane safety glass 6 mm, closes automatically

Door cover mask to equalise aisle height, 1 piece

Prepared for integration into door boxes, magnet detects when door is opened; connects to door plate

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	PU 2 pieces	1 piece	1 piece
1			2018	Adjustable feet			
2	42	2000	2102	Adjustable feet + raised top cover	21130-060	–	60130-065
3			2108	Base/plinth			
4			2192	Base/plinth + raised top cover			
5			2218	Adjustable feet		–	
6	47	2200	2302	Adjustable feet + raised top cover	21130-060	21130-040	60130-065
7			2308	Base/plinth		21130-040	
8			2392	Base/plinth + raised top cover		21130-059	

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 17

AUTOMATIC SLIDING DOORS

ORDER INFORMATION

		Automatic sliding door				
		RAL 7021	Cover	Reed contact	Motion detector	Battery pack
		01012061	01012069	01015001	01015003	01015002
		Sliding door, frame, St, with single pane safety glass 6 mm, closes electrically by pushbutton	Door cover mask to equalise aisle height, 1 piece	Prepared for integration into door boxes, magnet detects when door is opened; connects to door plate	Prepared for mounting on door box, power supply via connector on door plate	Prepared for integration into door boxes

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	PU 2 pieces	1 piece	1 piece	1 piece	1 piece
1			2018	Adjustable feet					
2			2102	Adjustable feet + raised top cover					
3	42	2000	2108	Base/plinth	21130-073	–	60130-065	60130-067	60130-066
4			2192	Base/plinth + raised top cover					
5			2218	Adjustable feet		–			
6			2302	Adjustable feet + raised top cover		21130-040			
7	47	2200	2308	Base/plinth	21130-073	21130-040	60130-065	60130-067	60130-066
8			2392	Base/plinth + raised top cover		21130-059			

Note: sliding door main image ID 01012073.

Cabinets – Varistar ServicePLUS

TOP COVERS

ORDER INFORMATION

		Top cover		Universal profile to raise top cover	Assembly kit
		600 mm width	800 mm width		

01012074   01012050   01012051   01012052

| | | | | Frame, St; with single pane safety glass 7 mm, aisle width 1200 mm | | Al extrusion, RAL 7021, length 2400 mm, height 84 mm | Bracket to mount the universal top cover profile |

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	1 piece	1 piece	PU 2 pieces	PU 6 pieces
1			2018	Adjustable feet			–	–
2			2102	Adjustable feet + raised top cover			21130-594	23130-433
3	42	2000	2108	Base/plinth	21130-588	21130-589	–	–
4			2192	Base/plinth + raised top cover			21130-594	23130-433
5			2218	Adjustable feet			–	–
6			2302	Adjustable feet + raised top cover			21130-594	23130-433
7	47	2200	2308	Base/plinth	21130-588	21130-589	–	–
8			2392	Base/plinth + raised top cover			21130-594	23130-433

Part number in bold face type: ready for despatch within 2 working days
Part number in normal type: ready for despatch within 10 working days

nVent.com/SCHROFF | 19

ORDER INFORMATION

	Automatic top cover		Control unit for top covers	Power supply for control unit	Connection/ extension cable Length 1 m	Connection/ extension cable Length 2 m	Connection/ extension cable Length 5 m
	600 mm width	800 mm width					

01012074   01017053   01017002   01617001   01017056

| | | Frame St, 2 mm, RAL 7021; 7 mm laminated safety glass, length 1200 mm, electromagnet with 1200 mm connection cable, T-shaped connecting plug and fixing materials kit | Control unit for up to 12 automatic top covers, inputs: - 24 V_{DC} and 2 floating contacts; output: 24 V_{DC} | For power distribution of up to 12 automatic top covers, input 100 to 240 V_{AC}, output: 24 V_{DC}, 40 W | Cable with plug, 1 m | Cable with plug, 2 m | Cable with plug, 5 m |

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	1 piece	1 piece	1 piece	1 piece	1 piece	1 piece	1 piece
1			2018	Adjustable feet							
2			2102	Adjustable feet + raised top cover							
3	42	2000	2108	Base/plinth	21130-592	21130-593	23130-205	23130-227	23130-206	23130-207	23130-226
4			2192	Base/plinth + raised top cover							
5			2218	Adjustable feet							
6			2302	Adjustable feet + raised top cover							
7	47	2200	2308	Base/plinth	21130-592	21130-593	23130-205	23130-227	23130-206	23130-207	23130-226
8			2392	Base/plinth + raised top cover							

CABLE PANEL ADAPTER, COVERS BESIDE 19" PLANE, SOLID

ORDER INFORMATION

			Adaptors for cable routing			Covers beside 19" plane, solid, 600 mm cabinet width		
			for 1000 mm cabinet depth	for 1200 mm cabinet depth	Mounting bracket for cable route adaptor	for 70 mm recessed 19" plane	for 145 mm recessed 19" plane	for 220 mm recessed 19" plane
			\n01013006	\n01012075	\n01012076	\n01012053		
				St profile, RAL 7021; fits to cabinet with a mounting bracket and has drilled holes to bolt on cable panel	Bracket, St, 1.5 mm	Gasketing on left and right; Cover at top and bottom		
No.	For cabinet height H U / mm	Aisle height (lower edge) mm	Raising elements	PU 2 pieces	PU 2 pieces	PU 2 pieces	PU 1 kit	PU 1 kit	PU 1 kit
1	42 / 2000	2018	Adjustable feet	**21130-596**	21130-597	21130-598	**21130-624**	21130-618	21130-622
2		2102	Adjustable feet + raised top cover						
3		2108	Base/plinth						
4		2192	Base/plinth + raised top cover						
5	47 / 2200	2218	Adjustable feet	**21130-596**	21130-597	21130-598	**21130-625**	21130-619	21130-626
6		2302	Adjustable feet + raised top cover						
7		2308	Base/plinth						
8		2392	Base/plinth + raised top cover						

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 21

COVERS BESIDE 19" PLANE, 800 MM, WITH ADAPTER BRACKET FOR REDUCED WIDTH

ORDER INFORMATION

01013006

01012055

Cover left, right, at top and bottom

01012054

Cover with cable routes left and right;
cover closed top and bottom

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	Cover, beside 19" plane, 800 mm cabinet width			Cover with lateral cut-outs		
					for 70 mm recessed 19" plane	for 145 mm recessed 19" plane	for 220 mm recessed 19" plane	for 70 mm recessed 19" plane	for 145 mm recessed 19" plane	for 220 mm recessed 19" plane
					PU 1 kit	PU 1 kit	PU 1 kit	PU 1 kit	PU 1 kit	PU 1 kit
1			2018	Adjustable feet						
2			2102	Adjustable feet + raised top cover						
3	42	2000	2108	Base/plinth	21130-627	21130-631	21130-633	21130-629	21130-620	21130-623
4			2192	Base/plinth + raised top cover						
5			2218	Adjustable feet						
6			2302	Adjustable feet + raised top cover						
7	47	2200	2308	Base/plinth	21130-628	21130-632	21130-634	21130-630	21130-621	21130-635
8			2392	Base/plinth + raised top cover						

Cabinets – Varistar ServicePLUS

COVERS WITH CABLE DUCTING, CABLE FINGER, CABLE CHANNEL

ORDER INFORMATION

				Covers beside 19" plane, 800 mm cabinet width, with cross member		Cover with cable fingers for 220 mm recessed 19" plane	Cover with cable channels	Cable panel
				Cover, solid	Cover with cable ducting openings			Lateral cable ducting
				01015054	01015055	01012056	01012077	01012078
				Cover with cable ducting left and right; cover at top, bottom solid, for 19" planes recessed to different depths (25 mm increments)		Support with cable fingers and front covers	St, with cable channel and hinged front cover	St, 1 mm, width 150 mm; with perforations for cable ties or Velcro-type tape
No.	For cabinet height H U mm	Aisle height (lower edge) mm	Raising elements	PU 1 kit	PU 1 kit	PU 1 kit	PU 1 kit	PU 2 pieces
1	42 2000	2018	Adjustable feet	23130-550	23130-558	21130-636	21130-638	**23130-421**
2		2102	Adjustable feet + raised top cover					
3		2108	Base/plinth					
4		2192	Base/plinth + raised top cover					
5	47 2200	2218	Adjustable feet	23130-551	23130-559	21130-637	21130-639	**23130-422**
6		2302	Adjustable feet + raised top cover					
7		2308	Base/plinth					
8		2392	Base/plinth + raised top cover					

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 23

19" PLASTIC FRONT PANELS, LATERAL PANELS

ORDER INFORMATION

			Closure for cut-outs in covers		Lateral panel	
			19" plastic panels	19" brush strip	Depth offset 70 mm	Depth offset 145 mm
			01012079	01012080	01012057	
01013006			ABS, UL 94 V-0, clips in To close the open cable routes in lateral panels	Plastic for sealing the open cable ducting openings of the lateral trim; 6 brushes, sufficient for 3 cutouts	Al, 2 mm Lateral panel for unequal 19" mounting depths	
No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	PU 10 pieces	PU 6 pieces	1 piece	1 piece
---	---	---	---	---	---	---	---	---
1			2018	Adjustable feet				
2			2102	Adjustable feet + raised top cover				
3	42	2000	2108	Base/plinth	**D19BPT1RU**	23130-153	21130-640	21130-642
4			2192	Base/plinth + raised top cover				
5			2218	Adjustable feet				
6			2302	Adjustable feet + raised top cover				
7	47	2200	2308	Base/plinth	**D19BPT1RU**	23130-153	21130-641	21130-643
8			2392	Base/plinth + raised top cover				

AIRFLOW FOR SIDE-TO-SIDE-COOLED SWITCHES

ORDER INFORMATION

				Basic kit for Cisco switches Air circulation from right to left	Side trims for Cisco switches						
					Switch 4503	Switch 4506	Switch 4507	Switch 4510	Switch 6506	Switch 6509	Switch 6513

01013006

01013060

Bezels, top cover and base plate for Cisco side trims

01012051

AlZn, 1 mm; multiple side plates can be fitted one above another; in all cases only one basic kit is required

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	PU 1 kit	1 piece	1 piece	1 piece	1 piece	1 piece	1 piece	1 piece
1			2018	Adjustable feet								
2	42	2000	2102	Adjustable feet + raised top cover	21130-646	23130-490	23130-491	23130-492	23130-493	23130-494	23130-495	23130-496
3			2108	Base/plinth								
4			2192	Base/plinth + raised top cover								
5			2218	Adjustable feet								
6	47	2200	2302	Adjustable feet + raised top cover	21130-647	23130-490	23130-491	23130-492	23130-493	23130-494	23130-495	23130-496
7			2308	Base/plinth								
8			2392	Base/plinth + raised top cover								

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 25

ORDER INFORMATION

		Separating wall		Vertical gasket	Horizontal gasket	
		Cabinet depth 1000 mm	Cabinet depth 1200 mm		For 600 mm wide cabinets	For 800 mm wide cabinets
		01012058		01012081	01012082	
		St, 1 mm; lateral cabinet mounting, prevents unauthorised access		PUR flexible foam, colour similar to RAL 7021, UL 94-HF1; for vertical sealing between 10 cabinets, also suitable for base/plinth and to raise top cover	2 x bracket, St, RAL 7021; PUR flexible foam seal, colour similar to RAL 7021, UL 94-HF1; suitable for horizontal sealing of 2 cabinets to bottom, when adjustable feet are used	
01013006						

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	1 piece	1 piece	PU 1 kit	PU 1 kit	PU 1 kit
1			2018	Adjustable feet					
2			2102	Adjustable feet + raised top cover					
3	42	2000	2108	Base/plinth	23130-480	23130-481	23130-475	23130-477	23130-478
4			2192	Base/plinth + raised top cover					
5			2218	Adjustable feet					
6			2302	Adjustable feet + raised top cover					
7	47	2200	2308	Base/plinth	23130-484	23130-485	23130-475	23130-477	23130-478
8			2392	Base/plinth + raised top cover					

CONFIGURATION OF SHX 30 AIR/WATER HEAT EXCHANGER

ORDER INFORMATION

				Frame		SHX 30 air/water heat exchanger, 30 kW			
				1000 mm deep	1200 mm deep	Water connection at bottom		Water connection at top and bottom (with condensate pump)	
				01013068 Rack (VARISTAR Slim-Line), St, RAL 7021; top cover and base plate, front and rear panel; prepared to accommodate SHX 30 air/water heat exchanger		01013076 2 PSUs, redundant power supply	1 PSU	01013077 2 PSUs, redundant power supply	
	For cabinet height H		Aisle height (lower edge)	Raising elements					
No.	U	mm	mm		1 piece	1 piece	1 piece	1 piece	1 piece	1 piece
1			2018	Adjustable feet						
2			2102	Adjustable feet + raised top cover						
3	42	2000	2108	Base/plinth	10130-226	10130-227	60714-067	60714-068	60714-077	60714-078
4			2192	Base/plinth + raised top cover						
5			2218	Adjustable feet						
6			2302	Adjustable feet + raised top cover						
7	47	2200	2308	Base/plinth	10130-228	10130-229	60714-067	60714-068	60714-077	60714-078
8			2392	Base/plinth + raised top cover						

01013005

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 27

CONFIGURATION OF SHX 30 AIR/WATER HEAT EXCHANGER

ORDER INFORMATION

				Adjustable feet	Gasketing for adjustable feet	Base/plinth	Side trim for base/plinth	
							Depth 1000 mm	Depth 1200 mm
				St, black, for the rack, static load-carrying capacity 1000 kg. Please order gasketing separately	Polyurethane gasketing, suitable for front and rear, RAL 7021; for closing the air gap at the front	Base plinth, St, cover, St, 1.5 mm, height 100 mm, width 300 mm, RAL 7021; please order cover separately	St, 1.5 mm, height 100 mm, RAL 7021	
				01013069	01013070	01013071	01013072	

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	PU 4 pieces	PU 2 pieces	PU 1 kit	PU 2 pieces	PU 2 pieces
1			2018	Adjustable feet					
2			2102	Adjustable feet + raised top cover					
3	42	2000	2108	Base/plinth	23130-511	23130-538	23130-507	**23130-172**	23130-363
4			2192	Base/plinth + raised top cover					
5			2218	Adjustable feet					
6			2302	Adjustable feet + raised top cover					
7	47	2200	2308	Base/plinth	23130-511	23130-538	23130-507	**23130-172**	23130-363
8			2392	Base/plinth + raised top cover					

Cabinets – Varistar ServicePLUS

CONFIGURATION OF SHX 30 AIR/WATER HEAT EXCHANGER

ORDER INFORMATION

				Screw-fixed side panel		Separating wall	
				Depth 1000 mm	Depth 1200 mm	Cabinet depth 1000 mm	Cabinet depth 1200 mm
				01013073		01013074	
				St, 1 mm, incl. GND/earthing		St, 1 mm, AlZn; lateral cabinet mounting prevents unauthorized access	
	For cabinet height H		Aisle height (lower edge)	Raising elements			
No.	U	mm	mm	PU 2 pieces	PU 2 pieces	1 piece	1 piece
1			2018	Adjustable feet			
2			2102	Adjustable feet + raised top cover			
3	42	2000	2108	Base/plinth	21130-013	21130-535	23130-480	23130-481
4			2192	Base/plinth + raised top cover			
5			2218	Adjustable feet			
6			2302	Adjustable feet + raised top cover			
7	47	2200	2308	Base/plinth	21130-018	21130-537	23130-484	23130-485
8			2392	Base/plinth + raised top cover			

01013005

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 29

CONFIGURATION OF SHX 30 AIR/WATER HEAT EXCHANGER

ORDER INFORMATION

				Top cover 300 mm width	Raised top cover	Assembly kit
				01013079	01012051	01012052
				St, 2 mm, RAL 7021, aisle width 1200 mm	Al extrusion, RAL 7021, length 2400 mm, height 84 mm	Mounting of top cover raising profile

01013005

No.	For cabinet height H U	mm	Aisle height (lower edge) mm	Raising elements	1 piece	PU 2 pieces	PU 6 pieces
1			2018	Adjustable feet		–	–
2	42	2000	2102	Adjustable feet + raised top cover	21130-648	21130-594	23130-433
3			2108	Base/plinth		–	–
4			2192	Base/plinth + raised top cover		21130-594	23130-433
5			2218	Adjustable feet		–	–
6	47	2200	2302	Adjustable feet + raised top cover	21130-648	21130-594	23130-433
7			2308	Base/plinth		–	–
8			2392	Base/plinth + raised top cover		21130-594	23130-433

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 30

Part number in bold face type: ready for shipping within 2 working days
Part number in normal type: ready for shipping within 10 working days

nVent.com/SCHROFF | 31

Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   RAYCHEM   SCHROFF   TRACER

nVent.com/SCHROFF