

# CableTek Vertical Cable Management

## WHAT'S NEW

### CABLETEK VERTICAL CABLE MANAGEMENT IS NOW AVAILABLE IN WHITE AND HAS TWO NEW DESIGNS

#### CableTek DV

The top of the CableTek line now has five models with a white finish. These vertical cable managers mount on the sides of or between 2- and 4-post open frame racks. The front side of the manager provides support, management and high capacity for patch cords, while the back supports Cat 5e, 6, 6A and fiber optic cables.

#### HIGHLIGHTS

- White models have white fingers and doors
- White available in only 7-foot height; black available in 7-, 8- and 9-foot heights
- 6-in., 10-in. and 12-in. width options
- Single- and double-sided



#### CableTek DVA - Angled Cable Manager **NEW!**

New to the CableTek line, this design can reduce space requirements when racks are placed at right angles to one another. The doors can open in either direction and you can remove one or both for direct access. The area behind the doors is quite large, allowing for easier access to cables for routing between racks.

#### HIGHLIGHTS

- Potentially reduces space by using a right angle configuration
- Available in white or black finish
- 7-foot and 8-foot height available
- Split doors - open right, left or both and can be completely removed
- Massive cable management area



**CableTek EC Series**

The existing CableTek EC series benefits from a few improvements. We've added 5 models in white (doors and fingers) and have improved the snap-hinge for attaching the doors.

**HIGHLIGHTS**

- White models have white fingers and doors
- 7-foot height only; available in white and black
- 3-inch and 6-inch width
- Single- and double-sided (6-inch)
- New and improved door snap-hinge



Exploded view of the improved snap-hinge



Detail view of snap-hinge attached to cable duct finger

**North America**

Minneapolis, MN  
Tel: +1.763.421.2240  
Mexico City, Mexico  
Tel: +52.55.5280.1449  
Toronto, Canada  
Tel: +1.416.289.2770

**South America**

Sao Paulo, Brazil  
Tel: +55.11.5184.2100  
Boituva, Brazil  
Tel: +55.15.3363.9148

**Europe**

Betschdorf, France  
Tel: +33.3.88.90.64.90  
Straubenhardt, Germany  
Tel: +49.7082.794.0  
Dzierzoniow, Poland  
Tel: +48.74.64.63.900  
Assago, Italy  
Tel: +39.02.932.7141

**Middle East & Africa**

Dubai, United Arab Emirates  
Tel: +971.4.378.1700  
Bangalore, India  
Tel: +91.80.6715.2001

**Asia**

Shanghai, P.R. China  
Tel: +86.21.2412.6943  
Singapore  
Tel: +65.6768.5800  
Shin-Yokohama, Japan  
Tel: +81.45.476.0271  
Seoul, Korea  
Tel: +82.2.2129.7755  
Qingdao  
Tel: +86.532.8771.6101



[nVent.com](http://nVent.com)

Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**