

**PEMSA CABLE MANAGEMENT, S.A.**

C/Galileo Galilei, 22-24 P. E. La Garena  
28806 ALCALÁ DE HENARES. Madrid.  
Phone: +34 91 802 3488  
[www.pemsa-rejiband.com](http://www.pemsa-rejiband.com)  
[info@pemsa-rejiband.com](mailto:info@pemsa-rejiband.com)



**UK DECLARATION OF CONFORMITY**



**PEMSA CABLE MANAGEMENT**

Declares that the product:

**Rejiband 100, Rejiband 150, Rejiband 35, Rejiband 60, Rejiband BLACK C8, Rejiband Rapide,  
Rejiband SAFECu Wire mesh tray**

which references are listed in the Annex 1 of this declaration, installed in accordance with the manufacturer's instructions and installation standards, complies with the essential requirements of the regulation reference:

**Electrical and Equipment (Safety) Regulations 2016  
(S.I. 2016 No. 1101)**

In conformity with the following standards:

---

**BS EN 61537** CABLE MANAGEMENT, CABLE TRAY SYSTEMS AND CABLE LADDER SYSTEMS

This declaration is issued under the sole responsibility of the manufacturer

Ernesto Chenol Mora  
Offer Development, Quality and Market Director.

**UK DECLARATION OF CONFORMITY****Annex 1**

<b>Reference</b>	<b>Designation</b>
60211060	Rejiband 35x 60 wire mesh tray EZ
60211100	Rejiband 35x100 wire mesh tray EZ
60211150	Rejiband 35x150 wire mesh tray EZ
60211200	Rejiband 35x200 wire mesh tray EZ
60211300	Rejiband 35x300 wire mesh tray EZ
60211400	Rejiband 35x400 wire mesh tray EZ
60212060	Rejiband 60x 60 wire mesh tray EZ
60212100	Rejiband 60x100 wire mesh tray EZ
60212150	Rejiband 60x150 wire mesh tray EZ
60212200	Rejiband 60x200 wire mesh tray EZ
60212300	Rejiband 60x300 wire mesh tray EZ
60212400	Rejiband 60x400 wire mesh tray EZ
60212450	Rejiband 60x450 wire mesh tray EZ
60212500	Rejiband 60x500 wire mesh tray EZ
60212600	Rejiband 60x600 wire mesh tray EZ
60213100	Rejiband 100x100 wire mesh tray EZ
60213150	Rejiband 100x150 wire mesh tray EZ
60213200	Rejiband 100x200 wire mesh tray EZ
60213300	Rejiband 100x300 wire mesh tray EZ
60213400	Rejiband 100x400 wire mesh tray EZ
60213450	Rejiband 100x450 wire mesh tray EZ
60213500	Rejiband 100x500 wire mesh tray EZ
60213600	Rejiband 100x600 wire mesh tray EZ
60214100	Rejiband 77x100 wire mesh tray EZ
60214150	Rejiband 77x150 wire mesh tray EZ
60214200	Rejiband 77x200 wire mesh tray EZ
60214300	Rejiband 77x300 wire mesh tray EZ
60214400	Rejiband 77x400 wire mesh tray EZ
60214500	Rejiband 77x500 wire mesh tray EZ
60214600	Rejiband 77x600 wire mesh tray EZ
60216200	Rejiband 150x200 wire mesh tray EZ
60216300	Rejiband 150x300 wire mesh tray EZ
60216400	Rejiband 150x400 wire mesh tray EZ

## UK DECLARATION OF CONFORMITY

Reference	Designation
60216450	Rejiband 150x450 wire mesh tray EZ
60216500	Rejiband 150x500 wire mesh tray EZ
60216600	Rejiband 150x600 wire mesh tray EZ
60221060	Rejiband 35x 60 wire mesh tray BYCRO
60221100	Rejiband 35x100 wire mesh tray BYCRO
60221150	Rejiband 35x150 wire mesh tray BYCRO
60221200	Rejiband 35x200 wire mesh tray BYCRO
60221300	Rejiband 35x300 wire mesh tray BYCRO
60221400	Rejiband 35x400 wire mesh tray BYCRO
60222060	Rejiband 60x 60 wire mesh tray BYCRO
60222100	Rejiband 60x100 wire mesh tray BYCRO
60222150	Rejiband 60x150 wire mesh tray BYCRO
60222200	Rejiband 60x200 wire mesh tray BYCRO
60222300	Rejiband 60x300 wire mesh tray BYCRO
60222400	Rejiband 60x400 wire mesh tray BYCRO
60222450	Rejiband 60x450 wire mesh tray BYCRO
60222500	Rejiband 60x500 wire mesh tray BYCRO
60222600	Rejiband 60x600 wire mesh tray BYCRO
60223100	Rejiband 100x100 wire mesh tray BYCRO
60223150	Rejiband 100x150 wire mesh tray BYCRO
60223200	Rejiband 100x200 wire mesh tray BYCRO
60223300	Rejiband 100x300 wire mesh tray BYCRO
60223400	Rejiband 100x400 wire mesh tray BYCRO
60223450	Rejiband 100x450 wire mesh tray BYCRO
60223500	Rejiband 100x500 wire mesh tray BYCRO
60223600	Rejiband 100x600 wire mesh tray BYCRO
60226200	Rejiband 150x200 wire mesh tray BYCRO
60226300	Rejiband 150x300 wire mesh tray BYCRO
60226400	Rejiband 150x400 wire mesh tray BYCRO
60226450	Rejiband 150x450 wire mesh tray BYCRO
60226500	Rejiband 150x500 wire mesh tray BYCRO
60226600	Rejiband 150x600 wire mesh tray BYCRO
60231060	Rejiband 35x 60 wire mesh tray GC
60231100	Rejiband 35x100 wire mesh tray GC
60231150	Rejiband 35x150 wire mesh tray GC
60231200	Rejiband 35x200 wire mesh tray GC
60231300	Rejiband 35x300 wire mesh tray GC
60231400	Rejiband 35x400 wire mesh tray GC

## UK DECLARATION OF CONFORMITY

Reference	Designation
60232060	Rejiband 60x 60 wire mesh tray GC
60232100	Rejiband 60x100 wire mesh tray GC
60232150	Rejiband 60x150 wire mesh tray GC
60232200	Rejiband 60x200 wire mesh tray GC
60232300	Rejiband 60x300 wire mesh tray GC
60232400	Rejiband 60x400 wire mesh tray GC
60232500	Rejiband 60x500 wire mesh tray GC
60232600	Rejiband 60x600 wire mesh tray GC
60233100	Rejiband 100x100 wire mesh tray GC
60233150	Rejiband 100x150 wire mesh tray GC
60233200	Rejiband 100x200 wire mesh tray GC
60233300	Rejiband 100x300 wire mesh tray GC
60233400	Rejiband 100x400 wire mesh tray GC
60233450	Rejiband 100x450 wire mesh tray GC
60233500	Rejiband 100x500 wire mesh tray GC
60233600	Rejiband 100x600 wire mesh tray GC
60236200	Rejiband 150x200 wire mesh tray GC
60236300	Rejiband 150x300 wire mesh tray GC
60236400	Rejiband 150x400 wire mesh tray GC
60236450	Rejiband 150x450 wire mesh tray GC
60236500	Rejiband 150x500 wire mesh tray GC
60236600	Rejiband 150x600 wire mesh tray GC
60251060	Rejiband 35x 60 wire mesh tray I304
60251100	Rejiband 35x100 wire mesh tray I304
60251150	Rejiband 35x150 wire mesh tray I304
60251200	Rejiband 35x200 wire mesh tray I304
60251300	Rejiband 35x300 wire mesh tray I304
60251400	Rejiband 35x400 wire mesh tray I304
60252060	Rejiband 60x 60 wire mesh tray I304
60252100	Rejiband 60x100 wire mesh tray I304
60252150	Rejiband 60x150 wire mesh tray I304
60252200	Rejiband 60x200 wire mesh tray I304
60252300	Rejiband 60x300 wire mesh tray I304
60252400	Rejiband 60x400 wire mesh tray I304
60252500	Rejiband 60x500 wire mesh tray I304
60252600	Rejiband 60x600 wire mesh tray I304
60253100	Rejiband 100x100 wire mesh tray I304
60253150	Rejiband 100x150 wire mesh tray I304

## UK DECLARATION OF CONFORMITY

Reference	Designation
60253200	Rejiband 100x200 wire mesh tray I304
60253300	Rejiband 100x300 wire mesh tray I304
60253400	Rejiband 100x400 wire mesh tray I304
60253500	Rejiband 100x500 wire mesh tray I304
60253600	Rejiband 100x600 wire mesh tray I304
60256200	Rejiband 150x200 wire mesh tray I304
60256300	Rejiband 150x300 wire mesh tray I304
60256400	Rejiband 150x400 wire mesh tray I304
60256450	Rejiband 150x450 wire mesh tray I304
60256500	Rejiband 150x500 wire mesh tray I304
60256600	Rejiband 150x600 wire mesh tray I304
60261060	Rejiband 35x 60 wire mesh tray I316L
60261100	Rejiband 35x100 wire mesh tray I316L
60261150	Rejiband 35x150 wire mesh tray I316L
60261200	Rejiband 35x200 wire mesh tray I316L
60261300	Rejiband 35x300 wire mesh tray I316L
60261400	Rejiband 35x400 wire mesh tray I316L
60262060	Rejiband 60x 60 wire mesh tray I316L
60262100	Rejiband 60x100 wire mesh tray I316L
60262150	Rejiband 60x150 wire mesh tray I316L
60262200	Rejiband 60x200 wire mesh tray I316L
60262300	Rejiband 60x300 wire mesh tray I316L
60262400	Rejiband 60x400 wire mesh tray I316L
60262500	Rejiband 60x500 wire mesh tray I316L
60262600	Rejiband 60x600 wire mesh tray I316L
60263100	Rejiband 100x100 wire mesh tray I316L
60263150	Rejiband 100x150 wire mesh tray I316L
60263200	Rejiband 100x200 wire mesh tray I316L
60263300	Rejiband 100x300 wire mesh tray I316L
60263400	Rejiband 100x400 wire mesh tray I316L
60263500	Rejiband 100x500 wire mesh tray I316L
60263600	Rejiband 100x600 wire mesh tray I316L
60266200	Rejiband 150x200 wire mesh tray I316L
60266300	Rejiband 150x300 wire mesh tray I316L
60266400	Rejiband 150x400 wire mesh tray I316L
60266450	Rejiband 150x450 wire mesh tray I316L
60266500	Rejiband 150x500 wire mesh tray I316L
60266600	Rejiband 150x600 wire mesh tray I316L

## UK DECLARATION OF CONFORMITY

Reference	Designation
60281060	Rejiband 35x 60 wire mesh tray BLACK C8
60281100	Rejiband 35x100 wire mesh tray BLACK C8
60281150	Rejiband 35x150 wire mesh tray BLACK C8
60281200	Rejiband 35x200 wire mesh tray BLACK C8
60281300	Rejiband 35x300 wire mesh tray BLACK C8
60281400	Rejiband 35x400 wire mesh tray BLACK C8
60282060	Rejiband 60x 60 wire mesh tray BLACK C8
60282100	Rejiband 60x100 wire mesh tray BLACK C8
60282150	Rejiband 60x150 wire mesh tray BLACK C8
60282200	Rejiband 60x200 wire mesh tray BLACK C8
60282300	Rejiband 60x300 wire mesh tray BLACK C8
60282400	Rejiband 60x400 wire mesh tray BLACK C8
60282450	Rejiband 60x450 wire mesh tray BLACK C8
60282500	Rejiband 60x500 wire mesh tray BLACK C8
60282600	Rejiband 60x600 wire mesh tray BLACK C8
60283100	Rejiband 100x100 wire mesh tray BLACK C8
60283150	Rejiband 100x150 wire mesh tray BLACK C8
60283200	Rejiband 100x200 wire mesh tray BLACK C8
60283300	Rejiband 100x300 wire mesh tray BLACK C8
60283400	Rejiband 100x400 wire mesh tray BLACK C8
60283450	Rejiband 100x450 wire mesh tray BLACK C8
60283500	Rejiband 100x500 wire mesh tray BLACK C8
60283600	Rejiband 100x600 wire mesh tray BLACK C8
60286200	Rejiband 150x200 wire mesh tray BLACK C8
60286300	Rejiband 150x300 wire mesh tray BLACK C8
60286400	Rejiband 150x400 wire mesh tray BLACK C8
60286450	Rejiband 150x450 wire mesh tray BLACK C8
60286500	Rejiband 150x500 wire mesh tray BLACK C8
60286600	Rejiband 150x600 wire mesh tray BLACK C8
60512060	Rapide wire mesh tray 60x 60-2 EZ
60512100	Rapide wire mesh tray 60x100 EZ
60512150	Rapide wire mesh tray 60x150 EZ
60512200	Rapide wire mesh tray 60x200 EZ
60512300	Rapide wire mesh tray 60x300 EZ
60512400	Rapide wire mesh tray 60x400 EZ
60512450	Rapide wire mesh tray 60x450 EZ
60512500	Rapide wire mesh tray 60x500 EZ
60512600	Rapide wire mesh tray 60x600 EZ

## UK DECLARATION OF CONFORMITY

Reference	Designation
60513100	Rapide wire mesh tray 100x100 EZ
60513150	Rapide wire mesh tray 100x150 EZ
60513200	Rapide wire mesh tray 100x200 EZ
60513300	Rapide wire mesh tray 100x300 EZ
60513400	Rapide wire mesh tray 100x400 EZ
60513450	Rapide wire mesh tray 100x450 EZ
60513500	Rapide wire mesh tray 100x500 EZ
60513600	Rapide wire mesh tray 100x600 EZ
60522060	Rapide wire mesh tray 60x60-2 BYCRO
60522100	Rapide wire mesh tray 60x100 BYCRO
60522150	Rapide wire mesh tray 60x150 BYCRO
60522200	Rapide wire mesh tray 60x200 BYCRO
60522300	Rapide wire mesh tray 60x300 BYCRO
60522400	Rapide wire mesh tray 60x400 BYCRO
60522450	Rapide wire mesh tray 60x450 BYCRO
60522500	Rapide wire mesh tray 60x500 BYCRO
60522600	Rapide wire mesh tray 60x600 BYCRO
60523100	Rapide wire mesh tray 100x100 BYCRO
60523150	Rapide wire mesh tray 100x150 BYCRO
60523200	Rapide wire mesh tray 100x200 BYCRO
60523300	Rapide wire mesh tray 100x300 BYCRO
60523400	Rapide wire mesh tray 100x400 BYCRO
60523450	Rapide wire mesh tray 100x450 BYCRO
60523500	Rapide wire mesh tray 100x500 BYCRO
60523600	Rapide wire mesh tray 100x600 BYCRO
60582060	Rapide wire mesh tray 60x 60-2 BLACK C8
60582100	Rapide wire mesh tray 60x100 BLACK C8
60582150	Rapide wire mesh tray 60x150 BLACK C8
60582200	Rapide wire mesh tray 60x200 BLACK C8
60582300	Rapide wire mesh tray 60x300 BLACK C8
60582400	Rapide wire mesh tray 60x400 BLACK C8
60582450	Rapide wire mesh tray 60x450 BLACK C8
60582500	Rapide wire mesh tray 60x500 BLACK C8
60582600	Rapide wire mesh tray 60x600 BLACK C8
60583100	Rapide wire mesh tray 100x100 BLACK C8
60583150	Rapide wire mesh tray 100x150 BLACK C8
60583200	Rapide wire mesh tray 100x200 BLACK C8
60583300	Rapide wire mesh tray 100x300 BLACK C8

**PEMSA CABLE MANAGEMENT, S.A.**

C/Galileo Galilei, 22-24 P. E. La Garena

28806 ALCALÁ DE HENARES. Madrid.

Phone: +34 91 802 3488

[www.pemsa-reiband.com](http://www.pemsa-reiband.com)[info@pemsa-reiband.com](mailto:info@pemsa-reiband.com)**UK DECLARATION OF CONFORMITY**

Reference	Designation
60583400	Rapide wire mesh tray 100x400 BLACK C8
60583450	Rapide wire mesh tray 100x450 BLACK C8
60583500	Rapide wire mesh tray 100x500 BLACK C8
60583600	Rapide wire mesh tray 100x600 BLACK C8
82003241	Rejiband SAFECu 60x100x2 m CU
82003242	Rejiband SAFECu 60x150x2 m CU
82003243	Rejiband SAFECu 60x200x2 m CU
82003244	Rejiband SAFECu 60x300x2 m CU
82003245	Rejiband SAFECu 60x450x2 m CU
82003247	Rejiband SAFECu 60x600x2 m CU
82003248	Rejiband SAFECu 100x100x2 m CU
82003249	Rejiband SAFECu 100x150x2 m CU
82003250	Rejiband SAFECu 100X200x2 m CU
82003251	Rejiband SAFECu 100X300x2 m CU
82003252	Rejiband SAFECu 100X450x2 m CU
82003254	Rejiband SAFECu 100X600x2 m CU