


Stripping-Tool-SR-Cable

CONNECT AND PROTECT

Stripping tool for nVent RAYCHEM self-regulating cables

PRODUCT OVERVIEW



The nVent RAYCHEM Stripping-Tool-SR-Cable is designed for use with nVent RAYCHEM BTV-CR, BTV-CT, QTVR-CT, XTV-CT, HTV-CT, HWAT, XL-Trace, IceStop and RaySol self-regulating heat-tracing cables. The tool is designed for faster, safer and more reliable cable terminations.

The tool has two sets of blades designed for precise scoring of the outer and inner jackets of the cables mentioned above. The scoring blades are protected by a spring-loaded cap that rotates automatically. For safety, the cap rotates back to its original position automatically after the cutting operation is performed.

The tool also includes a unique core scoring feature that prevents damage to the conductors. The tool has a robust metallic body, ergonomic contour and replaceable blades.



PRODUCT SPECIFICATIONS

Technical details

Body	Symmetric and Ergonomic Aluminum A380 Metallic Body with TPE soft sleeve.
Jacket scoring blades	A pair of jacket scoring stainless steel blades with depth ranges of 0.04–0.06 inch (1–1.5 mm) and 0.01–0.03 inch (0.25–0.75 mm).
Blade cover	Spring loaded Zinc alloy cap that covers both the blades when the tool is not in use.
Core scoring feature	Core scoring blade which will prevent damage to the conductors. The blade height should be 0.01–0.04 inch (0.25–1 mm).
Replaceable blades	All blades can be replaced with a screwdriver. Replaceable blades are provided with the tool.
Coating	Metallic body coated with electrostatic epoxy powder 0.002–0.005 inch (0.05–0.1 mm) thick.

ORDERING INFORMATION

	Catalog Number	Part Number
Stripping tool	Stripping-Tool-SR-Cable	P000001126
Replacement jacket scoring blade	Techni Edge® #10 Hobby blade TE01-103	Should be ordered directly from Techni Edge.
Replacement jacket slitting blade	Techni Edge 3/8 inch (9.5 mm) 13 point blade TE01-333	Should be ordered directly from Techni Edge.

APPROVALS

EAC (Russia, Kazakhstan, Belarus)
For other countries contact your local nVent representative.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nVent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nVent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nVent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nVent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER