

ProLine Frames

DOUBLE-BAY FRAMES

ProLine offers the broadest range of standard sizes in the industry.

SPECIFICATIONS

- Welded corners with steel corner blocks that add strength and rigidity
- 2,5 mm roll-formed frame sections for strength
- Flange on door and side openings deflects liquids away from the enclosure interior
- Rectangular frame holes are designed for metric cage nut fasteners
- Round frame holes allow numerous grounding locations using M5 thread-forming screws
- Access to both sides of frame mounting holes allows standard components to be easily installed
- Provisions for slide-in subpanel, rack mounting and accessory mounting
- Simple means for joining frames to create multiple-bay enclosures
- An open roll-formed profile design affords complete surface corrosion protection and assembly access




- Sealed mounting for all external accessories
- Center post on rear bottom and top, for more strength
- Sealed mounting for all external accessories
- Rear cover possible to mount on the back, rear door possible only as modification.
- Finished with RAL 7035 textured, gray polyester powder paint



STANDARD PRODUCT

Item number	Size H x W x d [mm]	Nominal Size H x W x D [mm]	Maximum Mounting Plate Size [mm]	Maximum Rack Mounting Space
PF14125	1380 x 1199 x 488	1400 x 1200 x 500	1285 x 1130	28U x 2
PF16125	1580 x 1199 x 488	1600 x 1200 x 500	1485 x 1130	33U x 2
PF18124	1780 x 1199 x 388	1800 x 1200 x 400	1685 x 1130	38U x 2
PF18125	1780 x 1199 x 488	1800 x 1200 x 500	1685 x 1130	38U x 2
PF18126	1780 x 1199 x 588	1800 x 1200 x 600	1685 x 1130	38U x 2
PF18128	1780 x 1199 x 788	1800 x 1200 x 800	1685 x 1130	38U x 2
PF20124	1980 x 1199 x 388	2000 x 1200 x 400	1885 x 1130	42U x 2
PF20125	1980 x 1199 x 488	2000 x 1200 x 500	1885 x 1130	42U x 2
PF20126	1980 x 1199 x 588	2000 x 1200 x 600	1885 x 1130	42U x 2
PF20128	1980 x 1199 x 788	2000 x 1200 x 800	1885 x 1130	42U x 2
PF22125	2180 x 1199 x 488	2200 x 1200 x 500	2085 x 1130	47U x 2
PF22126	2180 x 1199 x 588	2200 x 1200 x 600	2085 x 1130	47U x 2
PF22128	2180 x 1199 x 788	2200 x 1200 x 800	2085 x 1130	47U x 2

ProLine Frames



NOTE:
 1. Includes frame and frame nuts (12) to attach exterior components



87414907



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER