

nVent CADDY Rod Lock Plywood Form Preset Anchor



FEATURES GUIDE

SAFETY FEATURES

No need for overhead drilling or power tools

Large head makes it easier to hammer onto plywood forms

Included nails don't protrude from the plastic flange, limiting risk of injury while handling the product

Nails easily break off with a strike of a hammer once the plywood forms are removed

Plastic flange to avoid concrete intrusion

The color of the line corresponds to the larger goal of each feature:

SAFETY FEATURES

FASTER INSTALL FEATURES

STRENGTH FEATURES

FASTER INSTALL FEATURES

Long nails integrated in the product, securely holding the anchor in place to the wooden form during the pour and reducing the likelihood of knock over

Three additional thru-holes allowing the product to be mounted onto metal form using a nail gun

Plastic flange acts as insert locator when the forms are removed

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Works with slightly damaged threads and minor burrs on the threaded rod

Color-coded to help to identify the size (Blue for 3/8" and Yellow for 1/2")

STRENGTH FEATURES

Cast-in-place anchor is the strongest type of structural attachment and preserves the integrity of the concrete slab

Available in both 3/8" and 1/2" to provide the required strength for the services being supported

Compliant with 2015, 2012, and 2009 International Building Code® (IBC) and 2015, 2012, and 2009 International Residential Code® (IRC)

ICC-ES ESR-3864 Evaluation Report according to AC408, Acceptance Criteria for Headed Cast-In Specialty Inserts in Concrete

To be included in OSHPD OPM-0062-13 by 10/1/17 for use with nVent CADDY Seismic Bracing for Fire Sprinkler Piping


UL 203, ULC/ORD-C203 listed when used with a hex nut (see Instruction Sheet CFS479). Product underwent 100-hour vibration and passed

Compliant with UL 2043

FM 1951/52/53 approved

Can be used for an NFPA 13 – Fire Protection Installation

Suitable for cracked and uncracked concrete and seismic loading



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

WARNING

nVent products shall be installed and used only as indicated in Pentair's product instruction sheets and training materials. Instruction sheets are available at nVent.com/CADDY and from your Pentair customer service representative. Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

©2018 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.

CADDY-WPCS-FM1314WNAEN-RodLockPlywood-NAEN-1805