


ERIFLEX Flexibar Advanced nVent

ERIFLEX

WYJĄTKOWY- BEZPIECZNIEJSZY - ELASTYCZNY





ERIFLEX FLEXIBAR ADVANCED to unikalny, bezpieczniejszy i elastyczny przewód, który łączy 3 funkcje, aby poprawić bezpieczeństwo ludzi i urządzeń elektrycznych.

ERIFLEX ustanawia nowe standardy na rynku elektrycznym oferując wyjątkową izolację, która jest niskodymna, bezhalogenowa i trudnopalna przy zachowaniu odpowiedniego poziomu elastyczności i niezawodności ERIFLEX FLEXIBAR.

ERIFLEX FLEXIBAR ADVANCED optymalizuje zagospodarowanie przestrzeni, zmniejsza koszt instalacji dzięki swojej elastyczności, poprawia niezawodność i bezpieczeństwo instalacji elektrycznej.





Oszczędność miejsca i masy

- Wymaga mniej miejsca na instalację niż przewód okrągły
- Zmniejsza długość, ilość i masę przewodów
- Izolacja umożliwia mniejsze odstępy niż przy użyciu tradycyjnych szynoprzewodów

Oszczędności

- Eliminuje koszty i instalację występow
- Zmniejsza koszty zapasów

Poprawia niezawodność

- Połączenie jest wykonywane bezpośrednio do szyny ERIFLEX FLEXIBAR ADVANCED, bez potrzeby stosowania końcówki
- Doskonała odporność na wibracje
- Bez zaciskania

Estetyka

- Ułatwia optymalne rozplanowanie i dostęp do elementów rozdzielnic

Łatwość instalacji

- Instalacja jest prosta dzięki łatwości gięcia i kształtowania nawet szyn o dużych przekrojach

Odniesienie	Opis	Pakowanie	Odniesienie	Opis	Pakowanie
534058	FLEXIBAR ADVANCED 2 m Tinned copper 10X100X1	1	534044	FLEXIBAR ADVANCED 2 m Tinned copper 4X63X1	1
534060	FLEXIBAR ADVANCED 2 m Tinned copper 10X120X1	1	534049	FLEXIBAR ADVANCED 2 m Tinned copper 4X80X1	1
534009	FLEXIBAR ADVANCED 2 m Tinned copper 10X15,5X0,8	4	534055	FLEXIBAR ADVANCED 2 m Tinned copper 5X100X1	1
534015	FLEXIBAR ADVANCED 2 m Tinned copper 10X20X1	3	534013	FLEXIBAR ADVANCED 2 m Tinned copper 5X20X1	3
534022	FLEXIBAR ADVANCED 2 m Tinned copper 10X24X1	3	534019	FLEXIBAR ADVANCED 2 m Tinned copper 5X24X1	3
534029	FLEXIBAR ADVANCED 2 m Tinned copper 10X32X1	2	534026	FLEXIBAR ADVANCED 2 m Tinned copper 5X32X1	2
534036	FLEXIBAR ADVANCED 2 m Tinned copper 10X40X1	2	534033	FLEXIBAR ADVANCED 2 m Tinned copper 5X40X1	2
534042	FLEXIBAR ADVANCED 2 m Tinned copper 10X50X1	1	534039	FLEXIBAR ADVANCED 2 m Tinned copper 5X50X1	1
534048	FLEXIBAR ADVANCED 2 m Tinned copper 10X63X1	1	534045	FLEXIBAR ADVANCED 2 m Tinned copper 5X63X1	1
534053	FLEXIBAR ADVANCED 2 m Tinned copper 10X80X1	1	534050	FLEXIBAR ADVANCED 2 m Tinned copper 5X80X1	1
534059	FLEXIBAR ADVANCED 2 m Tinned copper 12X100X1	1	534056	FLEXIBAR ADVANCED 2 m Tinned copper 6X100X1	1
534006	FLEXIBAR ADVANCED 2 m Tinned copper 2X15,5X0,8	4	534005	FLEXIBAR ADVANCED 2 m Tinned copper 6X13X0,5	4
534010	FLEXIBAR ADVANCED 2 m Tinned copper 2X20X1	3	534008	FLEXIBAR ADVANCED 2 m Tinned copper 6X15,5X0,8	4
534016	FLEXIBAR ADVANCED 2 m Tinned copper 2X24X1	3	534014	FLEXIBAR ADVANCED 2 m Tinned copper 6X20X1	3
534023	FLEXIBAR ADVANCED 2 m Tinned copper 2X32X1	2	534020	FLEXIBAR ADVANCED 2 m Tinned copper 6X24X1	3
534030	FLEXIBAR ADVANCED 2 m Tinned copper 2X40X1	2	534027	FLEXIBAR ADVANCED 2 m Tinned copper 6X32X1	2
534004	FLEXIBAR ADVANCED 2 m Tinned copper 3X13X0,5	4	534034	FLEXIBAR ADVANCED 2 m Tinned copper 6X40X1	2
534011	FLEXIBAR ADVANCED 2 m Tinned copper 3X20X1	3	534040	FLEXIBAR ADVANCED 2 m Tinned copper 6X50X1	1
534017	FLEXIBAR ADVANCED 2 m Tinned copper 3X24X1	3	534046	FLEXIBAR ADVANCED 2 m Tinned copper 6X63X1	1
534024	FLEXIBAR ADVANCED 2 m Tinned copper 3X32X1	2	534051	FLEXIBAR ADVANCED 2 m Tinned copper 6X80X1	1
534031	FLEXIBAR ADVANCED 2 m Tinned copper 3X40X1	2	534002	FLEXIBAR ADVANCED 2 m Tinned copper 6X9X0,8	4
534037	FLEXIBAR ADVANCED 2 m Tinned copper 3X50X1	1	534057	FLEXIBAR ADVANCED 2 m Tinned copper 8X100X1	1
534001	FLEXIBAR ADVANCED 2 m Tinned copper 3X9X0,8	4	534021	FLEXIBAR ADVANCED 2 m Tinned copper 8X24X1	3
534007	FLEXIBAR ADVANCED 2 m Tinned copper 4X15,5X0,8	4	534028	FLEXIBAR ADVANCED 2 m Tinned copper 8X32X1	2
534012	FLEXIBAR ADVANCED 2 m Tinned copper 4X20X1	3	534035	FLEXIBAR ADVANCED 2 m Tinned copper 8X40X1	2
534018	FLEXIBAR ADVANCED 2 m Tinned copper 4X24X1	3	534041	FLEXIBAR ADVANCED 2 m Tinned copper 8X50X1	1
534025	FLEXIBAR ADVANCED 2 m Tinned copper 4X32X1	2	534000	FLEXIBAR ADVANCED 2 m Tinned copper 8X6X0,5	4
534032	FLEXIBAR ADVANCED 2 m Tinned copper 4X40X1	2	534047	FLEXIBAR ADVANCED 2 m Tinned copper 8X63X1	1
534038	FLEXIBAR ADVANCED 2 m Tinned copper 4X50X1	1	534052	FLEXIBAR ADVANCED 2 m Tinned copper 8X80X1	1
			534003	FLEXIBAR ADVANCED 2 m Tinned copper 9X9X0,8	4

North America

+1-440-248-0100 Tel
+1-440-248-0723 Fax
nVent.com/ERIFLEX

Europe, Middle East, Africa

+31-13-583-5100 Tel
+31-13-583-5499 Fax
nVent.com/ERIFLEX

Asia Pacific

+86-21-2412 1617 Tel
+86-21-5426 5167 Fax
nVent.com/ERIFLEX

Latin America

+52 55 3686-9785 Tel
+52-55-5260-3310 Fax
nVent.com/ERIFLEX



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER