


Perfect Trim Adjustable Mud Ring and Accessories





CONNECT AND PROTECT

NVENT CADDY PERFECT TRIM ADJUSTABLE MUD RING

The nVent CADDY Perfect Trim Adjustable Mud Ring system provides multiple options for configuration and offers a flush installation to the finished surface in almost any application. Designed to be used as a conventional style adjustable mud ring with the option to adjust for single and double layer drywall.

In addition, the inner ring can be easily removed from the outer ring to create a second method of positioning allowing the device to be installed with the inner ring after the drywall has been installed. This method allows for a rigid cover plate to be snapped into place protecting the box contents, making drywall cutout step easier and more precise around the outer ring, and reducing drywall rework. Our system reduces total install time, eliminates potential damage to pre-installed devices, and makes drywall installation easier and more reliable.





Features

- Two piece adjustable mud ring accommodates various thicknesses of drywall
- Inner ring is removable which allows devices to be installed after drywall installation
- Can be used with nVent CADDY Perfect Trim Protector Plate (sold separately) that snaps into outer ring after inner ring has been removed to prevent damage during drywall installation
- Can be used with nVent CADDY Perfect Trim Clip (sold separately) that snaps into inner ring to hold box bracket flush and rigid to drywall
- Can be used with nVent CADDY Perfect Trim Extension Ring (sold separately) that attaches to inner ring for additional depths up to 2¼"
- Designed for U.S. plaster ring and cover screw locations

Material: Steel
Finish: Pregalvanized




Part Number	Box Size	Gang	Drywall Thickness	A	B	Height H	Thickness T	Unit Weight
PTDG4	4"	2	5/8" - 1 1/4"	4.10"	4.10"	0.625" - 1.450"	1/16"	0.45 lb
PTDG411	4 1/16"	2	5/8" - 1 1/4"	4.68"	4.68"	0.625" - 1.450"	1/16"	0.54 lb
PTSG4	4"	1	5/8" - 1 1/4"	4.10"	4.10"	0.625" - 1.450"	1/16"	0.46 lb
PTSG411	4 1/16"	1	5/8" - 1 1/4"	4.68"	4.68"	0.625" - 1.450"	1/16"	0.56 lb



Perfect Trim Accessories


Innovative nVent CADDY Perfect Trim Extension Rings can be added to extend the working depth of the adjustable mud ring before or after drywall has been installed. Optional nVent CADDY Perfect Trim Clips snap into place and help repair and eliminate box pushback into the wall space. The reusable nVent CADDY Perfect Trim Protector Plate snaps in to place to protect the electrical wiring and content inside the box during installation.



NVENT CADDY PERFECT TRIM CLIP



Material: Spring Steel
Finish: Pregalvanized



Features


- Clips easily snap into slots within the inner ring creating a surface to catch drywall
- Tightening the Adjustable Mud Ring screws creates a flush, rigid application after drywall has been installed

Part Number	A	B	Height H	Thickness T	Unit Weight
PTC	0.31"	3.9"	0.78"	0.04"	0.02 lb

NVENT CADDY PERFECT TRIM PROTECTOR PLATE



Material: Steel
Finish: Pregalvanized



Features

- Innovative design, snaps into place to protect wiring and contents inside of the box
- Center opening provides means to quickly remove cover plate for access to the inside of the box
- The flat rigid surface makes drywall cutout step easier, faster, and more precise


Part Number	Gang	A	B	Height H	Thickness T	Unit Weight
PTP1	1	2.3"	3.9"	0.64"	0.04"	0.11 lb
PTP2	2	4.0"	3.8"	0.64"	0.04"	0.18 lb

PTP1 is used with single gang Perfect Trim Adjustable Mud Ring (PTSG4 and PTSG411).
PTP2 is used with double gang Perfect Trim Adjustable Mud Ring (PTDG4 and PTDG411).

NVENT CADDY PERFECT TRIM EXTENSION RING



Material: Steel
Finish: Pregalvanized



Features

- Extension Ring easily installs with two screws (included) to extend working depth of nVent CADDY Perfect Trim Adjustable Mud Rings to 2¼"
- Can be installed for extension purposes after drywall and tile installation

Part Number	Gang	A	B	Height H	Width W	Thickness T	Unit Weight
PTDGEX	2	3.90"	3.65"	7/8"	1.1"	1/16"	0.25 lb
PTSGEX	1	2.13"	3.72"	7/8"	1.1"	1/16"	0.19 lb



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER