



nVent CADDY Pyramid Light-Duty Equipment Support



CONNECT AND PROTECT



The nVent CADDY Pyramid Light-Duty Equipment Support Kit provides contractors with a quick and easy way to install HVAC mini split units on rooftops. When utilized with the nVent CADDY Pyramid Light-Duty Equipment Support Frame Extension Kit or the nVent CADDY Pyramid Light-Duty Equipment Support Crossbar, installers can link multiple HVAC units. The unique attachment clamps and frame design allow for a more flexible and efficient installation method, saving contractors time, money and space.



Features

- System takes 80% less time to install compared to standard options on the market
- Easily adjusts from 12–18 in (305–457 mm), reducing the need for multiple SKUs
- Increased adjustability enables flexibility to move bars, sliding the kit as needed
- Extension Kit allows for pre-assembly and endless gang-ability of units linked together
- Evenly distributes load and avoids damaging roof membrane with nVent CADDY PEK-style foam bottom feet
- Product load rating can handle wide range of equipment BTU outputs/sizes
- Hot dip galvanized construction and hardware provide superior corrosion resistance in demanding environments


NVENT CADDY PYRAMID LIGHT-DUTY EQUIPMENT SUPPORT KIT, 4 POST BASE



Material: Steel
Finish: Hot-Dip Galvanized

Part Number	Temperature	Height H	Length L	Post Base A	Square Tube B	Cross Bar Assembly C	Width W	Surface Area	Unit Weight	Ultimate Static Load F
PEKLD4	-34.4 to 54.4°C	305 – 457 mm	1052 mm	152 mm x 4 pc	970.28 mm x 2 pc	521 mm x 2 pc	660 mm	0.092 m ²	14.6 kg	1779 N

NVENT CADDY PYRAMID LIGHT-DUTY EQUIPMENT SUPPORT KIT EXTENSION FRAME




Material: Steel
Finish: Hot-Dip Galvanized

Additional features

- Extension Kit is 8.4 in (213 mm) longer than four-post kit to allow for mounted equipment to be serviced in place

Part Number	Temperature	Height H	Length L	Post Base A	Square Tube B	Cross Bar Assembly C	Width W	Surface Area	Unit Weight	Ultimate Static Load F
PEKLDEF	-34.4 to 54.4°C	305 – 457 mm	1265 mm	152 mm x 2 pc	1224.28 mm x 2 pc	521 mm x 2 pc	660 mm	0.046 m ²	11.5 kg	1779 N

NVENT CADDY PYRAMID LIGHT-DUTY EQUIPMENT SUPPORT CROSSBAR



Additional features

- Conveniently sold as a pair of bars
- Quickly install by simply sliding the bar over the system and fastening the screws
- Hot dip galvanized construction and hardware provide superior corrosion resistance in demanding environments

Part Number	Package Unit	Width W	Length L
PEKLDCB	Pair	76.2 mm	559.75 mm



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO RAYCHEM SCHROFF