

This authorizes the application of the Certification Mark(s) shown below to the models described in the Product(s) Covered section when made in accordance with the conditions set forth in the Certification Agreement and Listing Report. This authorization also applies to multiple listee model(s) identified on the correlation page of the Listing Report.

This document is the property of Intertek Testing Services and is not transferable. The certification mark(s) may be applied only at the location of the Party Authorized To Apply Mark.

Applicant:	Nemalux Inc.	Manufacturer:	Nemalux Inc.
Address:	1018 72 Ave NE Calgary, AB T2E 8V9	Address:	1018 72 Ave NE Calgary, AB T2E 8V9
Country:	Canada	Country:	Canada
Party Authorized To Apply Mark:	Same as Manufacturer		
Report Issuing Office:	Intertek Testing Services (ITS) Ltd, Edmonton, Alberta		

Control Number: 3185954 **Authorized by:** *Kerem Lasery*
for L. Matthew Snyder, Certification Manager



This document supersedes all previous Authorizations to Mark for the noted Report Number.

This Authorization to Mark is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Authorization to Mark. Only the Client is authorized to permit copying or distribution of this Authorization to Mark and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement and in this Authorization to Mark. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.

Intertek Testing Services NA Inc.
545 East Algonquin Road, Arlington Heights, IL 60005
Telephone 800-345-3851 or 847-439-5667 Fax 312-283-1672

	Luminaires for Use in Hazardous (Classified) Locations [UL 844:2012 Ed.13+R:22Jul2020]
	Electric Luminaires for use in Hazardous Locations [CSA C22.2#137:2018 Ed.2]
Standard(s):	Nonincendive Electrical Equipment for Use in Class I and II, Division 2 and Class III, Divisions 1 and 2 Hazardous (Classified) Locations [UL 121201:2017 Ed.9+R:01Apr2021]
	Nonincendive Electrical Equipment for Use in Class I and II, Division 2 and Class III, Divisions 1 and 2 Hazardous (Classified) Locations [CSA C22.2#213:2017 Ed.3+U1;U2;U3]
Product:	Models XCANLEDac, XCANLEDdc, CANLED and GSLEDIP are for use in the following Classified Location: Class I, Division 2, Groups ABCD Temperature Code: T3 Model XCANLEDac: -40°C to 45°C Models XCANLEDdc, CANLED and GSLEDIP: -40°C to 65°C

CANLED; followed by -; followed by 50, 45, 40, 35, 30, 27, 65, RE, BL, GR, AM; followed by -W, -WF, -N, -NF; followed by -ALU, -BLK; followed by -C1D2.

CANLED; followed by -; followed by two characters; followed by -; followed by up to three characters; followed by -; followed by three letters; followed by -C1D2.

GSLEDIP; followed by -; followed by 12, 24, 36 or 48; followed by 50, 45, 40, 35, 30, 27, 65, RE, BL, GR, AM, CW/RE, CW/BL; followed by -W, -WF, -N, -NF; followed by -WHT, -BLK; followed by -C1D2; followed by -12VDC or -24VDC.

GSLEDIP; followed by -; followed by 12, 24, 36 or 48; followed by up to five characters; followed by -; followed by up to three characters; followed by -; followed by three letters; followed by -C1D2; followed by -12VDC or -24VDC.

Models:

XCANLEDDC; followed by -; followed by 50, 45, 40, 35, 30, 27, 65, RE, BL, GR, AM; followed by -W, -WF, -N, -NF; followed by -ALU, -BLK; followed by -C1D2.

XCANLEDDC; followed by -; followed by two characters; followed by -; followed by up to three characters; followed by -; followed by three letters; followed by -C1D2.

XCANLEDAC; followed by -; followed by 50, 45, 40, 35, 30, 27, 65, RE, BL, GR, AM; followed by -W, -WF, -N, -NF; followed by -ALU, -BLK; followed by -C1D2.

XCANLEDAC; followed by -; followed by two characters; followed by -; followed by up to three characters; followed by -; followed by three letters; followed by -C1D2.