




REAR VIEW



SIDE VIEW



FRONT VIEW



BOTTOM VIEW

SEE SHEET 2 FOR ADDITIONAL LAYOUT DETAILS

TECHNICAL SPECIFICATIONS	
UNIT TYPE:	MONITORED SWITCHED
ORIENTATION:	VERTICAL, 0U MID
OUTLET QTY & TYPE:	(18) 5-20R
INPUT VOLTAGE:	100-120VAC
INPUT CURRENT:	30A (24A DERATED)
BREAKER QTY & TYPE:	(2) 20AMP, SINGLE-POLE
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	2.9kVA
INPUT PLUG:	SEE NOTE 7
INPUT POWER CORD:	SEE IDENTIFICATION TABLE
FEATURES	
METERING ACCURACY	+/-1% TO ISO/ IEC 62052-21
METERING ATTRIBUTES	VOLTAGE(V), CURRENT(A), APPARENT POWER(kVA), REAL POWER(kW), POWER FACTOR, ENERGY(kWh)
METERED COMPONENTS	INPUT(PHASE), CIRCUIT BREAKERS
REMOTE OUTLET SWITCHING	YES
ENVIRONMENTAL CONDITIONS	
OPERATING TEMPERATURE	-5 TO 60 C (23 TO 140 F)
STORAGE TEMPERATURE	-20 TO 60 C (-4 TO 140 F)
HUMIDITY (OPERATING/STORAGE)	5-90% RH / 5-95% RH; NON-CONDENSING
MAX OPERATING ELEVATION, ABOVE MSL	3000M(9840FT)
COMPLIANCE	
SAFETY&ENVIRONMENTAL	RoHS COMPLIANT






IDENTIFICATION TABLE	EN2319-	*	*	*	*	*
MODEL IS SHOWN IN DEFAULT CONFIGURATION. FOR OPTIONAL CONFIGURATIONS, USE ITEM IDENTIFIER CODE IN PLACE OF EACH ASTERISK. ORDERABLE BASED ON FORMAT: EN##### **	INPUT PLUG (DEFAULT) L5-30P=0	CHASSIS COLOR (DEFAULT) BLACK = 0 BLUE = B RED = R WHITE = W GREEN = G YELLOW = Y	CORD OPTION (DEFAULT) 3m [10'] = 0 1m [3.2'] = 1 2m [6.6'] = 2	ORIENTATION (DEFAULT) TOP FEED = 0 BOTTOM FEED = 2	JP	
OPTIONS LISTED ON THIS ROW ARE NON STANDARD, CONTACT SALES FOR ADDITIONAL INFORMATION		ORANGE = A	0.5m [1.6'] = A 1.2m [4'] = G 1.5m [4.9'] = B 1.8m [6'] = F 2.5m [8.2'] = C			

- NOTES :
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
  - PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
  - UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR 3RD PARTY ENCLOSURES. BRACKET IS PROVIDED WITH THE UNIT.
  - DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE QUICK START GUIDE
  - CONNECT EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT
  - SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
  - INPUT PLUG CONFIGURATION (SEE IDENTIFICATION TABLE) FOR DUAL-RATED UNITS, NEMA PLUGS ARE NAM RATED ONLY AND CAPTIVE AUS/NZ PLUGS ARE EMEA RATED ONLY



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

REVISIONS		PART NO:		REV.
---	E1	EN2319-0000JP_DA		E1
ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED
		INITIAL DRAFT REVIEW	2023/10/11	LRF
TITLE:		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:		
Advantage Series Metered Switched		X: ±1 MM X*: ±1"		
		X.X ±0.5 MM X.X* ±0.5"		
PROJECT: <b>enLOGIC</b>		Φ.XX ±0.20 MM		
		Φ.XX ±0.3 MM		
		BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY		
		⊕ THRID ANGLE PROJECTION		
		INTERPRET PER ASME Y14.5M-1994		
		SCALE: N/A		SHEET 1 OF 3
				A3



**NOTES:**  
 1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.  
 2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION

**enLOGIC** by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

**TITLE:**  
 Advantage Series  
 Metered Switched

**PROJECT:**  
 enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:  
 X: ±1 MM X\*: ±1"  
 X.X ±0.5 MM X.X\* ±0.5"  
 X.XX ±0.20 MM  
 ØX.X ±0.3 MM  
 ØX.XX ±0.10 MM

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY  
 THRID ANGLE PROJECTION  
 INTERPRET PER ASME Y14.5M-1994

<b>PART NO:</b> EN2319-0000JP_DA	<b>REV.</b> E1
<b>DRAWN BY:</b> LRF	2023/10/11
<b>ENGINEER:</b> LJB	2023/10/11
<b>APPROVED BY:</b> Hanson	2023/10/12
<b>SCALE:</b> N/A	<b>SIZE:</b> A3
SHEET 2 OF 3	

# enLOGIC

## RACK Power Distribution Unit

Metered Switched

Made In XXXXX (Factory ID: X)

SKU#



Serial Number



SKU #: EN2319-0000JP  
Model #: EP23024-0022  
INPUT: 100-120VAC, 1PHASE, 50/60Hz, 24A  
OUTPUT: 5-20R; 100-120VAC, 16A per outlet  
24A Total



エヌロジックジャパン株式会社  
100-120VAC 24A

Mfr.Name:XXXXXXXXXXXXXXXXXXXXXXXXXXXX

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES. OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS:  
(1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE.  
AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED, INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRABLE OPERATION.  
CAN ICES-3(A)/NMB-3(A)


### NOTES:

#### 1. INTERNAL WIRING:

WIRE TYPE: UL AWM 1015, 12 & 18AWG  
LINE 1/R/X COLOR: BLACK  
EARTH GROUND COLOR: GREEN/YELLOW STRIPE  
NEUTRAL WIRE COLOR: WHITE

#### 2. FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

### COMPLIANCE LABEL



### INTERNAL WIRING SCHEMATIC

### NOTES:

- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
- SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
- THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

### TITLE:

Advantage Series  
Metered Switched

### PROJECT:

enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:

X	±1	MM	X*	±1°
X.X	±0.5	MM	X.X*	±0.5°
X.XX	±0.20	MM		
∅X.X	±0.3	MM		
∅X.XX	±0.10	MM		

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY

THIRD ANGLE PROJECTION

INTERPRET PER ASME Y14.5M-1994

PART NO: EN2319-0000JP\_DA

DRAWN BY: LRF

ENGINEER: LJB

APPROVED BY: Hanson

SCALE: N/A

### REV.

E1

2023/10/11

2023/10/11

2023/10/12

SHEET 3 OF 3

A3