




REAR VIEW



SIDE VIEW



FRONT VIEW



BOTTOM VIEW

TECHNICAL SPECIFICATIONS	
UNIT TYPE:	MONITORED INPUT
ORIENTATION:	VERTICAL, MID
OUTLET QTY & TYPE:	(24) 5-20R
INPUT VOLTAGE:	100-120VAC
INPUT CURRENT:	30A (24A DERATED)
BREAKER QTY & TYPE:	(2) 20AMP, SINGLE-POLE
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	2.9kVA
INPUT PLUG:	SEE NOTE 7
INPUT POWER CORD:	SEE IDENTIFICATION TABLE
FEATURES	
METERING ACCURACY	+/-1% TO ISO/ IEC 62052-21
METERING ATTRIBUTES	VOLTAGE(V), CURRENT(A), APPARENT POWER(kVA), REAL POWER(kW), POWER FACTOR, ENERGY(kWh)
METERED COMPONENTS	INPUT(PHASE), CIRCUIT BREAKERS
REMOTE OUTLET SWITCHING	N/A
ENVIRONMENTAL CONDITIONS	
OPERATING TEMPERATURE	-5 TO 60 C (23 TO 140 F)
STORAGE TEMPERATURE	-20 TO 60 C (-4 TO 140 F)
HUMIDITY (OPERATING/STORAGE)	5-90% RH / 5-95% RH; NON-CONDENSING
MAX OPERATING ELEVATION, ABOVE MSL	3000M(9840FT)
COMPLIANCE	
SAFETY&ENVIRONMENTAL	RoHS COMPLIANT

IDENTIFICATION TABLE	EN 1327-	*	*	*	*	*
MODEL IS SHOWN IN DEFAULT CONFIGURATION. FOR OPTIONAL CONFIGURATIONS, USE ITEM IDENTIFIER CODE IN PLACE OF EACH ASTERISK. ORDERABLE BASED ON FORMAT: EN##### **	INPUT PLUG (DEFAULT) L5-30P=0	CHASSIS COLOR (DEFAULT) BLACK = 0 BLUE = B RED = R WHITE = W GREEN = G YELLOW = Y	CORD OPTION (DEFAULT) 3m [10'] = 0 1m [3.2'] = 1 2m [6.6'] = 2	ORIENTATION (DEFAULT) TOP FEED = 0 BOTTOM FEED = 2	JP	
OPTIONS LISTED ON THIS ROW ARE NON STANDARD, CONTACT SALES FOR ADDITIONAL INFORMATION		ORANGE = A	0.5m [1.6'] = A 1.2m [4'] = G 1.5m [4.9'] = B 1.8m [6'] = F 2.5m [8.2'] = C			



- NOTES :
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 - PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
 - UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR 3RD PARTY ENCLOSURES. BRACKET IS PROVIDED WITH THE UNIT.
 - DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE QUICK START GUIDE
 - CONNECT EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT
 - SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
 - INPUT PLUG CONFIGURATION (SEE IDENTIFICATION TABLE) FOR DUAL-RATED UNITS, NEMA PLUGS ARE NAM RATED ONLY AND CAPTIVE AUS/NZ PLUGS ARE EMEA RATED ONLY



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED
--	E1	INITIAL DRAFT REVIEW	2023/10/11	LRF
REVISIONS				
TITLE:		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:	PART NO:	REV.
Advantage Series Metered		X: ±1 MM X*: ±1"	EN1327-0000JP_DA	E1
		X.X: ±0.5 MM X.X*: ±0.5"	DRAWN BY: LRF	2023/10/11
PROJECT: enLOGIC		X.XX: ±0.2 MM	ENGINEER: LJB	2023/10/11
		φX.X: ±0.3 MM	APPROVED BY: Hanson	2023/10/12
		BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY	SCALE: N/A	SHEET 1 OF 3
		⊕ THIRD ANGLE PROJECTION		SIZE: A3
		INTERPRET PER ASME Y14.5M-1994		

LABEL DETAIL





20AMP, SINGLE-POLE ELECTRO MECHANICAL SWITCH / BREAKER (2)PLACES




RECEPTACLE

NEMA 5 - 20R
16A, 125V MAX
RATED OUTPUT



- Critical Alarm Alerts**
 - ▲ PDU Alarm
 - Cascade Error
 - Environmental Alarm
 - Security Alarm
 - Circuit Breaker Alarm
- Source Color Coding** (User Selected Option)
- User Interactive Display** (for setup and detailed information)
- 10/100 Ethernet Port** (for redundancy and Ethernet cascading)
- Digital Sensor Port 2**



NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION



THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
Advantage Series
Metered

PROJECT:
enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:
 X: ±1 MM X*: ±1"
 X.X: ±0.5 MM X.X*: ±0.5"
 X.XX: ±0.20 MM
 ØX.X: ±0.3 MM
 ØX.XX: ±0.10 MM

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY
 THIRD ANGLE PROJECTION
 INTERPRET PER ASME Y14.5M-1994

PART NO: EN1327-0000JP_DA	REV. E1
DRAWN BY: LRF	2023/10/11
ENGINEER: LJB	2023/10/11
APPROVED BY: Hanson	2023/10/12
SCALE: N/A	SHEET: 2 OF 3
	SIZE: A3

enLOGIC

RACK Power Distribution Unit

Made In XXXXX (Factory ID: X)

SKU#



Serial Number



SKU #: EN1327-0000JP
Model #: EP13024-0024
INPUT: 100-120VAC, 1PHASE, 50/60Hz, 24A
OUTPUT: C5-20R; 100-120VAC, 16A per outlet
24A Total



エヌイベントジャパン株式会社
 100-120VAC 24A


Mfr.Name:XXXXXXXXXXXXXXXXXXXXXXXXXXXX

MAC0 Address: XX-XX-XX-XX-XX-XX
MAC1 Address: XX-XX-XX-XX-XX-XX

NOTES:

- INTERNAL WIRING:**
 WIRE TYPE: UL AWM 1015, 12 & 18AWG
 LINE 1/R/X COLOR: BLACK
 EARTH GROUND COLOR: GREEN/YELLOW STRIPE
 NEUTRAL WIRE COLOR: WHITE
- FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION

COMPLIANCE LABEL



INTERNAL WIRING SCHEMATIC

- NOTES:**
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 - SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
 - THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
 Advantage Series
 Metered

PROJECT:
 enLOGIC

UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:
 X: ±1 MM X°: ±1°
 X.X: ±0.5 MM X.X°: ±0.5°
 X.XX: ±0.20 MM
 ØX.X: ±0.3 MM
 ØX.XX: ±0.10 MM

BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY
 Ⓢ THRID ANGLE PROJECTION
 INTERPRET PER ASME Y14.5M-1994

PART NO: EN1327-0000JP_DA	REV. E1
DRAWN BY: LRF	2023/10/11
ENGINEER: LJB	2023/10/11
APPROVED BY: Hanson	2023/10/12
SCALE: N/A	SIZE: SHEET 3 OF 3 A3