

TECHNICAL SPECIFICATIONS	
UNIT TYPE:	INPUT METERED
ORIENTATION:	VERTICAL, 0U
OUTLET QTY & TYPE:	(19)C13/C15LOCKING, (19)C13/C15/C19LOCKING
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	100A (80A DERATED)
BREAKER QTY & TYPE:	(9) 20AMP, DOUBLE-POLE ,10KA
INPUT PHASE:	THREE-PHASE (DELTA)
RATED POWER:	28.8kVA(NAM)
INPUT PLUG:	SEE NOTE 7
INPUT POWER CORD:	SEE IDENTIFICATION TABLE
FEATURES	
METERING ATTRIBUTES	VOLTAGE(V), CURRENT(A), APPARENT POWER(kVA), REAL POWER(kW), POWER FACTOR, ENERGY(kWh)
METERED COMPONENTS	INPUT(PHASE)
REMOTE OUTLET SWITCHING	NO
ENVIRONMENTAL CONDITIONS	
OPERATING TEMPERATURE	-5 TO 60 C (23 TO 140 F)
STORAGE TEMPERATURE	-20 TO 60 C (-4 TO 140 F)
HUMIDITY (OPERATING/STORAGE)	5-90% RH / 5-95% RH; NON-CONDENSING
MAX OPERATING ELEVATION, ABOVE MSL	3000M (9840 FT)
COMPLIANCE	
SAFETY & ENVIRONMENTAL	RoHS COMPLIANT





IDENTIFICATION TABLE	EN19HB -	* INPUT PLUG	* CHASSIS COLOR	* CORD OPTION	* ORIENTATION
MODEL IS SHOWN IN DEFAULT CONFIGURATION. FOR OPTIONAL CONFIGURATIONS, USE ITEM IDENTIFIER CODE IN PLACE OF EACH ASTERISK. ORDERABLE BASED ON FORMAT: EN19HB - * * * *		(DEFAULT) 4100P9W(IP67) = 0	(DEFAULT) BLACK = 0 BLUE = B RED = R WHITE = W GREEN = G YELLOW = Y	(DEFAULT) 1.8m [6'] = 0 1m [3.2'] = 1 2m [6.6'] = 2 3m [10'] = 3	(DEFAULT) TOP FEED = 0 BOTTOM FEED = 2
OPTIONS LISTED ON THIS ROW ARE NON STANDARD, CONTACT SALES FOR ADDITIONAL INFORMATION			ORANGE = A	0.5m [1.6'] = A 1.5m [4.9'] = B 2.5m [8.2'] = C 3.5m [11.4'] = D	4.5m [14.7'] = E 1.2m [4'] = G 3.65m [12'] = H 4m [13.2'] = 4

- NOTES:**
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 - PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
 - UNIVERSAL MOUNTING BRACKET IS AN ALTERNATIVE MOUNTING METHOD TO THE TOOLLESS MOUNT FOR 3RD PARTY ENCLOSURES. BRACKET IS PROVIDED WITH THE UNIT.
 - DETAILED INSTALLATION INSTRUCTIONS CAN BE FOUND IN THE QUICK START GUIDE
 - CONNECT EXTERNAL EARTH GROUND TO THE 10-32 SIZE THREADED NUT
 - SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
 - INPUT PLUG CONFIGURATION (SEE IDENTIFICATION TABLE) FOR DUAL-RATED UNITS, NEMA PLUGS ARE NAM RATED ONLY AND CAPTIVE AUS/NZ PLUGS ARE EMEA RATED ONLY

ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED
	E2	ADD THE HEIGHT DIMENSION AT THE NMC SEGMENT	2024/07/22	ZLF
	E1	INITIAL DRAFT REVIEW	2024/04/17	ZLF

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:	UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE:	PART NO:	REV.
ADVANTAGE SERIES INPUT METERED	X. ±1 MM X.X ±0.5 MM X.XX ±0.20 MM ØX.X ±0.3 MM ØX.XX ±0.10 MM	EN19HB-WXYZ_DA	E2
PROJECT: enLOGIC	BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY	DRAWN BY: ZLF	2024/04/17
	⊕ THRID ANGLE PROJECTION	ENGINEER: XY	2024/07/22
	INTERPRET PER ASME Y14.5M-1994	APPROVED BY: LJB	2024/07/22
		SCALE: N/A	SHEET 1 OF 3
			SIZE: A3



CIS-PEC-2407-0083	E2	ADD THE HEIGHT DIMENSION AT THE NMC SEGMENT	2024/07/22	ZLF
	E1	INITIAL DRAFT REVIEW	2024/04/17	ZLF
ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED

REVISIONS		PART NO:	REV.
TITLE:	ADVANTAGE SERIES INPUT METERED	EN19HB-WXYZ_DA	E2
PROJECT:	enLOGIC	DRAWN BY: ZLF	2024/04/17
		ENGINEER: XY	2024/07/22
		APPROVED BY: LJB	2024/07/22
		SCALE: N/A	SHEET 2 OF 3
			SIZE: A3

enLOGIC by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

NOTES:
 1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
 2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION

enLOGIC RACK Power Distribution Unit
Metered

SKU #: EN19HB-WXYZ
Model#: EP114080-0095-L
INPUT: 200-240VAC, DELTA, 3-PHASE, 50/60Hz, 80A
OUTPUT: C13/C15 LOCKING; 200-240VAC, 10A per outlet
C13/C15/C19 LOCKING; 200-240VAC, 16A max per outlet
80A Total

MAC0 Address:XX-XX-XX-XX-XX-XX
MAC1 Address:XX-XX-XX-XX-XX-XX

Made In XXXXX

FC SA 300805


SKU#: EN19HB-WXYZ
Serial Number XXXXXXXXXX

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES. OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS:
(1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE,
AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED, INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRABLE OPERATION.
CAN ICES-3(A)/NMB-3(A)

NOTES:
1. INTERNAL WIRING
WIRE TYPE: UL AWM-1015, 10 & 12 & 18 AWG
LINE 1/R/X COLOR: Black
LINE 2/S/Y COLOR: Orange
LINE 3/T/Z COLOR: Red
EARTH GROUND COLOR: Green/Yellow
2. FOR FINISHED GOOD PART NUMBER SEE IDENTIFICATION



COMPLIANCE LABEL



INTERNAL WIRING SCHEMATIC DIAGRAM

NOTES:
1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION
3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

enLOGIC by nvent

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF CIS GLOBAL AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM CIS GLOBAL. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE

CIS-PEC-2407-0083	E2	ADD THE HEIGHT DIMENSION AT THE NMC SEGMENT	2024/07/22	ZLF
	E1	INITIAL DRAFT REVIEW	2024/04/17	ZLF
ECN/ECO	REV.	DESCRIPTION	DATE	APPROVED
REVISIONS				
TITLE:		UNLESS NOTED, DIMENSIONS ARE IN MILLIMETERS & TOLERANCES ARE: X. ±1 MM X° ±1° X.X ±0.5 MM X.X° ±0.5° X.XX ±0.20 MM ØX.X ±0.3 MM ØX.XX ±0.10 MM	PART NO: EN19HB-WXYZ_DA	REV. E2
PROJECT:		BRACKETED DIMENSIONS ARE IN INCHES FOR REFERENCE ONLY	DRAWN BY: ZLF	2024/04/17
enLOGIC		THIRD ANGLE PROJECTION	ENGINEER: XY	2024/07/22
		INTERPRET PER ASME Y14.5M-1994	APPROVED BY: LJB	2024/07/22
			SCALE: N/A	SHEET 3 OF 3
				SIZE: A3