

# DT14 Terminator, Plain

## CONNECT AND PROTECT



The nVent LENTON Swaged Terminator system is designed to maximize operator safety and product performance while increasing shop productivity. The system is robust, allowing for the inherent variability of rebar while maintaining the highest level of performance.

The DT14 head area exceeds 10x bar area (net 9x). The system is designed to meet Caltrans Ultimate performance with A706 grade 60 rebar, ASTM A970 Classes A, HA, and B performance with A706 and A615 grade 60 and grade 80 rebar.

### FEATURES

- Eliminates reinforcing bar hooks and simplifies bar placement with greater design flexibility
- Minimizes embedment lengths and reduces congestion
- Simplifies concrete placement
- Terminators are permanently secured to the bar and will not loosen or fall off during transportation
- Fast installation makes them ideal for high-volume shear ties

Finish: Plain  
Material: Steel  
100% U.S. Domestic Content: Yes



Catalog Number	Rebar Size, Metric	Rebar Size, US	Diameter 1 (Ø1)		Diameter 2 (Ø2)		Length 1 (L1)		Length 2 (L2)		Unit Weight		Box Quantity
			inch	mm	inch	mm	inch	mm	inch	mm	lb	kg	
LS12DT14D	12	#4	1.63	41	1.38	35	1.51	38	0.31	8	0.6	0.27	50
LS16DT14D	16	#5	2.00	51	1.75	44	1.77	45	0.38	10	1.1	0.49	30
LS20DT14D	20	#6	2.38	60	1.94	49	2.25	57	0.38	10	1.7	0.77	20
LS22DT14D	22	#7	2.88	73	2.38	60	2.32	59	0.41	10	2.7	1.21	12
LS25DT14D	25	#8	3.25	83	2.75	70	2.58	66	0.41	10	4.0	1.80	8
LS28DT14D	28	#9	3.75	95	2.88	73	2.91	74	0.46	12	5.0	2.28	6

Designed to Meet: ACI 318; AS3600; ASTM A970; Caltrans Ultimate (A706 Grade 60)  
Terminator sizes #10 (LS32DT14D) and #11 (LS36DT14D) available soon. Contact your local sales representative for more information.

